

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P498866

Luminaire Tested: **LDA2B159030R65D010 2LBD1WH**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P498866  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-66)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/8/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B159030R65D010 2LBD1WH  
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 3000K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1148.1 lumens  
Efficiency: N/A  
Efficacy: 81.4 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.95  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 14.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P498866

CATALOG NUMBER: LDA2B159030R65D010 2LBD1WH

### Luminous Intensity Polar Plot





TEST NUMBER: P498866

CATALOG NUMBER: LDA2B159030R65D010 2LBD1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	111	108	106	111	109	106	104	104	103	101		101	99	98		97	96	95	93
2	108	103	99	95	106	101	97	94	98	95	92		95	92	90		92	90	88	87
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87	84	82	80
4	97	89	84	79	95	88	83	79	86	82	78		84	80	77		82	79	76	75
5	92	83	78	73	90	82	77	73	81	76	72		79	75	72		77	74	71	69
6	87	78	72	68	86	77	72	67	76	71	67		74	70	66		73	69	66	65
7	83	73	67	63	81	73	67	63	71	66	62		70	65	62		69	65	62	60
8	78	69	63	58	77	68	62	58	67	62	58		66	61	58		65	61	58	56
9	75	65	59	55	73	64	58	54	63	58	54		62	58	54		61	57	54	53
10	71	61	55	51	70	61	55	51	60	55	51		59	54	51		58	54	51	49

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	623807
5°	573693
10°	548214
15°	526497
20°	484913
25°	449101
30°	411484
35°	302226
40°	143170
45°	47096
50°	15197
55°	1978
60°	1085
65°	700
70°	865
75°	0
80°	0
85°	0



TEST NUMBER: P498866

CATALOG NUMBER: LDA2B159030R65D010 2LBD1WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	108.8	9.5
10°-20°	286.7	25.0
20°-30°	380.3	33.1
30°-40°	300.9	26.2
40°-50°	65.7	5.7
50°-60°	4.9	0.4
60°-70°	0.7	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	775.8	67.6
0°-40°	1076.6	93.8
0°-60°	1147.2	99.9
0°-90°	1148.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1148.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1264	
5°	1158	109
15°	1031	287
25°	825	380
35°	502	301
45°	68	66
55°	2	5
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P498866

CATALOG NUMBER: LDA2B159030R65D010 2LBD1WH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1264.4
1°	1257.6
2°	1234.3
3°	1208.8
4°	1182.2
5°	1158.4
6°	1143.1
7°	1127.7
8°	1117.5
9°	1102.2
10°	1094.3
11°	1081.8
12°	1067.6
13°	1055.2
14°	1041.0
15°	1030.8
16°	1004.7
17°	991.7
18°	970.1
19°	950.3
20°	923.6
21°	902.1
22.5°	873.7
23°	865.8
24°	844.2
25°	825.0
26°	813.1
27°	793.2
28°	773.9
29°	750.7
30°	722.3
32.5°	623.7
35°	501.8
37.5°	357.8
40°	222.3
42.5°	125.3
45°	67.5
47.5°	36.3
50°	19.8
52.5°	8.5
55°	2.3
57.5°	1.1
60°	1.1
62.5°	0.6
65°	0.6



TEST NUMBER: P498866

CATALOG NUMBER: LDA2B159030R65D010 2LBD1WH

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.6
70°	0.6
72.5°	0.6
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)