

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P498902

Luminaire Tested: **LDA2B159030R70D010 2LBDLC1MB**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P498902
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-81)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B159030R70D010 2LBDLC1MB
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 3000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1111.8 lumens
Efficiency: N/A
Efficacy: 78.8 lumens/watt
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P498902

CATALOG NUMBER: LDA2B159030R70D010 2LBDLC1MB

Luminous Intensity Polar Plot





TEST NUMBER: P498902

CATALOG NUMBER: LDA2B159030R70D010 2LBDLC1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	105	111	108	106	103	104	102	100		100	99	97		97	96	94	93
2	107	102	97	94	105	100	96	93	97	93	91		94	91	89		91	89	87	85
3	101	94	89	84	99	93	88	84	90	86	82		87	84	81		85	82	80	78
4	95	87	81	76	93	86	80	76	84	79	75		82	77	74		80	76	73	72
5	90	81	74	70	88	80	74	69	78	73	69		76	72	68		74	71	67	66
6	85	75	68	64	83	74	68	63	72	67	63		71	66	63		70	65	62	61
7	80	70	63	59	78	69	63	58	68	62	58		66	61	58		65	61	57	56
8	75	65	58	54	74	64	58	54	63	58	54		62	57	53		61	57	53	52
9	71	61	54	50	70	60	54	50	59	54	50		58	53	50		57	53	49	48
10	68	57	51	47	66	57	50	46	56	50	46		55	50	46		54	49	46	45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	440177
5°	437600
10°	434694
15°	426643
20°	411199
25°	393684
30°	375024
35°	309453
40°	201133
45°	105076
50°	48892
55°	17891
60°	1776
65°	1401
70°	865
75°	1144
80°	0
85°	0



TEST NUMBER: P498902

CATALOG NUMBER: LDA2B159030R70D010 2LBDLC1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.6	7.5
10°-20°	234.7	21.1
20°-30°	333.1	30.0
30°-40°	311.5	28.0
40°-50°	125.3	11.3
50°-60°	21.9	2.0
60°-70°	1.0	0.1
70°-80°	0.6	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
<hr/>		
0°-30°	651.4	58.6
0°-40°	963.0	86.6
0°-60°	1110.2	99.9
0°-90°	1111.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1111.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	892	
5°	884	84
15°	835	235
25°	723	333
35°	514	312
45°	151	125
55°	21	22
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P498902

CATALOG NUMBER: LDA2B159030R70D010 2LBDLC1MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	892.2
1°	893.4
2°	891.6
3°	887.9
4°	886.1
5°	883.6
6°	873.9
7°	876.9
8°	868.3
9°	866.5
10°	867.7
11°	859.8
12°	857.9
13°	848.1
14°	844.5
15°	835.3
16°	829.8
17°	818.7
18°	805.9
19°	798.5
20°	783.2
21°	771.6
22.5°	750.2
23°	744.6
24°	734.2
25°	723.2
26°	714.6
27°	702.4
28°	690.1
29°	675.4
30°	658.3
32.5°	598.3
35°	513.8
37.5°	414.0
40°	312.3
42.5°	222.9
45°	150.6
47.5°	99.2
50°	63.7
52.5°	39.8
55°	20.8
57.5°	6.7
60°	1.8
62.5°	1.2
65°	1.2



TEST NUMBER: P498902

CATALOG NUMBER: LDA2B159030R70D010 2LBDLC1MB

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.6
70°	0.6
72.5°	0.6
75°	0.6
77.5°	0.6
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)