

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P500357

Luminaire Tested: **LDA2B208030R60D010 2LBD1WMH**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P500357
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-53)
Test Lab: INNOVATION CENTER
Issue Date: 3/8/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B208030R60D010 2LBD1WMH
Description: 2000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 3000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1930.1 lumens
Efficiency: N/A
Efficacy: 93.7 lumens/watt
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.87
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 20.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P500357

CATALOG NUMBER: LDA2B208030R60D010 2LBD1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P500357

CATALOG NUMBER: LDA2B208030R60D010 2LBD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94				94
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88				88
3	103	97	92	88	101	96	91	88	93	89	86	91	87	85	88	86	84	82				82
4	98	91	86	81	96	90	85	81	88	83	80	86	82	79	84	81	78	77				77
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72				72
6	89	80	74	70	87	79	74	70	78	73	70	77	72	69	75	72	69	67				67
7	85	76	70	66	83	75	69	66	74	69	65	73	68	65	71	67	64	63				63
8	81	71	66	62	79	71	65	61	70	65	61	69	64	61	68	64	61	59				59
9	77	68	62	58	76	67	62	58	66	61	58	65	61	57	64	60	57	56				56
10	73	64	58	55	72	64	58	54	63	58	54	62	57	54	61	57	54	53				53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1155503
5°	1096971
10°	1073885
15°	1039459
20°	950347
25°	843765
30°	631211
35°	356311
40°	134153
45°	60074
50°	29243
55°	5849
60°	1973
65°	1167
70°	1442
75°	0
80°	0
85°	0



TEST NUMBER: P500357

CATALOG NUMBER: LDA2B208030R60D010 2LBD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	209.7	10.9
10°-20°	565.2	29.3
20°-30°	690.6	35.8
30°-40°	376.6	19.5
40°-50°	75.4	3.9
50°-60°	10.8	0.6
60°-70°	1.4	0.1
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1465.5	75.9
0°-40°	1842.2	95.4
0°-60°	1928.3	99.9
0°-90°	1930.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1930.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2342	
5°	2215	210
15°	2035	565
25°	1550	691
35°	592	377
45°	86	75
55°	7	11
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P500357

CATALOG NUMBER: LDA2B208030R60D010 2LBD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	2342.1
1°	2331.4
2°	2310.8
3°	2283.5
4°	2244.3
5°	2215.0
6°	2199.4
7°	2180.8
8°	2166.1
9°	2159.3
10°	2143.6
11°	2126.0
12°	2110.4
13°	2091.8
14°	2064.4
15°	2035.1
16°	1997.9
17°	1946.1
18°	1912.8
19°	1859.0
20°	1810.1
21°	1765.2
22.5°	1689.9
23°	1658.6
24°	1610.6
25°	1550.0
26°	1472.8
27°	1391.6
28°	1298.7
29°	1210.7
30°	1108.0
32.5°	849.8
35°	591.6
37.5°	370.6
40°	208.3
42.5°	130.1
45°	86.1
47.5°	58.7
50°	38.1
52.5°	19.6
55°	6.8
57.5°	2.9
60°	2.0
62.5°	2.0
65°	1.0



TEST NUMBER: P500357

CATALOG NUMBER: LDA2B208030R60D010 2LBD1WMH

CANDELA DISTRIBUTION (continued):

	0°
67.5°	1.0
70°	1.0
72.5°	1.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)