

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P278925

Luminaire Tested: **LDA2B159050D010 EU2B15NFL259050 2LBALD1B**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P278925  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-2)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA2B159050D010 EU2B15NFL259050 2LBALD1B  
Description: PORTFOLIO 2IN ADJ 1500 LUMEN LED LUMINAIRE WITH NARROW FLOOD OPTIC  
AND 2in ADJ spun Refl w/lens Self-Flanged, B  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1235.7 lumens  
Efficiency: N/A  
Efficacy: 87.6 lumens/watt  
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.39  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P278925

CATALOG NUMBER: LDA2B159050D010 EU2B15NFL259050 2LBALD1B

### Luminous Intensity Polar Plot





TEST NUMBER: P278925

CATALOG NUMBER: LDA2B159050D010 EU2B15NFL259050 2LBALD1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100									100																			
1	115	113	111	110	113	111	109	108	107	106	105	103	102	102	100	99	99	97									97																			
2	112	108	105	103	110	107	104	102	103	101	100	101	99	98	98	97	96	94									94																			
3	108	104	100	98	107	103	99	97	100	98	95	98	96	94	96	94	93	91									91																			
4	105	100	96	94	104	99	96	93	97	94	92	95	93	91	94	92	90	89									89																			
5	102	97	93	90	101	96	92	90	94	91	89	93	90	88	92	89	87	86									86																			
6	100	94	90	87	98	93	89	87	92	89	86	91	88	86	89	87	85	84									84																			
7	97	91	87	84	96	90	87	84	89	86	84	88	85	83	87	85	83	82									82																			
8	95	88	85	82	94	88	84	82	87	84	81	86	83	81	85	83	81	80									80																			
9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78									78																			
10	90	84	80	78	90	84	80	78	83	80	77	82	79	77	82	79	77	76									76																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	3162844
5°	2916951
10°	1965667
15°	969127
20°	413982
25°	162765
30°	64090
35°	28066
40°	13525
45°	6489
50°	3607
55°	1978
60°	1184
65°	700
70°	865
75°	0
80°	0
85°	0



TEST NUMBER: P278925

CATALOG NUMBER: LDA2B159050D010 EU2B15NFL259050 2LBALD1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	498.9	40.4
10°-20°	537.3	43.5
20°-30°	155.1	12.6
30°-40°	32.8	2.7
40°-50°	8.1	0.7
50°-60°	2.3	0.2
60°-70°	0.8	0.1
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1191.4	96.4
0°-40°	1224.1	99.1
0°-60°	1234.5	99.9
0°-90°	1235.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1235.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6411	
5°	5890	499
15°	1897	537
25°	299	155
35°	47	33
45°	9	8
55°	2	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P278925

CATALOG NUMBER: LDA2B159050D010 EU2B15NFL259050 2LBALD1B

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	6410.8
1°	6370.6
2°	6302.4
3°	6210.4
4°	6079.8
5°	5889.9
6°	5633.4
7°	5298.9
8°	4887.5
9°	4407.9
10°	3923.7
11°	3434.1
12°	2972.0
13°	2561.8
14°	2201.0
15°	1897.4
17.5°	1254.1
20°	788.5
22.5°	484.8
25°	299.0
27.5°	182.4
30°	112.5
32.5°	71.1
35°	46.6
37.5°	30.9
40°	21.0
42.5°	14.6
45°	9.3
47.5°	5.8
50°	4.7
52.5°	3.5
55°	2.3
57.5°	1.7
60°	1.2
62.5°	1.2
65°	0.6
67.5°	0.6
70°	0.6
72.5°	0.6
75°	0.0
77.5°	0.6
80°	0.0
82.5°	0.0



TEST NUMBER: P278925

CATALOG NUMBER: LDA2B159050D010 EU2B15NFL259050 2LBALD1B

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)