

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P500365

Luminaire Tested: **LDA2B208030R60D010 2LBDL1WH**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P500365  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-55)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B208030R60D010 2LBDL1WH  
Description: 2000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 3000K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1780.4 lumens  
Efficiency: N/A  
Efficacy: 86.4 lumens/watt  
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.86  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 20.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P500365

CATALOG NUMBER: LDA2B208030R60D010 2LBDL1WH

### Luminous Intensity Polar Plot





TEST NUMBER: P500365

CATALOG NUMBER: LDA2B208030R60D010 2LBDL1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82
4	98	90	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71
6	88	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67
7	84	75	69	65	83	74	69	65	73	68	65	72	68	64	71	67	64	63
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59
9	76	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55
10	73	63	58	54	72	63	58	54	62	57	54	61	57	54	61	57	53	52

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1053722
5°	1026249
10°	997938
15°	948543
20°	866658
25°	744201
30°	553791
35°	325113
40°	154956
45°	72353
50°	35997
55°	12644
60°	2861
65°	2335
70°	1442
75°	1906
80°	0
85°	0



TEST NUMBER: P500365

CATALOG NUMBER: LDA2B208030R60D010 2LBDL1WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	195.0	11.0
10°-20°	516.8	29.0
20°-30°	613.5	34.5
30°-40°	346.3	19.5
40°-50°	90.0	5.1
50°-60°	16.4	0.9
60°-70°	1.7	0.1
70°-80°	0.7	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1325.3	74.4
0°-40°	1671.6	93.9
0°-60°	1778.0	99.9
0°-90°	1780.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1780.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2136	
5°	2072	195
15°	1857	517
25°	1367	614
35°	540	346
45°	104	90
55°	15	16
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P500365

CATALOG NUMBER: LDA2B208030R60D010 2LBDL1WH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2135.8
1°	2136.8
2°	2122.1
3°	2109.4
4°	2084.9
5°	2072.2
6°	2049.7
7°	2033.1
8°	2017.5
9°	2006.7
10°	1992.0
11°	1963.7
12°	1937.3
13°	1922.6
14°	1888.4
15°	1857.1
16°	1820.9
17°	1777.9
18°	1736.8
19°	1687.9
20°	1650.7
21°	1599.9
22.5°	1515.8
23°	1501.1
24°	1429.7
25°	1367.1
26°	1297.7
27°	1217.5
28°	1138.3
29°	1061.1
30°	972.1
32.5°	748.1
35°	539.8
37.5°	368.7
40°	240.6
42.5°	157.4
45°	103.7
47.5°	70.4
50°	46.9
52.5°	29.3
55°	14.7
57.5°	5.9
60°	2.9
62.5°	2.0
65°	2.0



TEST NUMBER: P500365

CATALOG NUMBER: LDA2B208030R60D010 2LBDL1WH

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	1.0
70°	1.0
72.5°	1.0
75°	1.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)