

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P500369

Luminaire Tested: **LDA2B208030R60D010 2LBDLC1MMS**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P500369
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-55)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B208030R60D010 2LBDLC1MMS
Description: 2000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 3000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1930.1 lumens
Efficiency: N/A
Efficacy: 93.7 lumens/watt
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.86
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 20.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P500369

CATALOG NUMBER: LDA2B208030R60D010 2LBDLC1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P500369

CATALOG NUMBER: LDA2B208030R60D010 2LBDLC1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	101		101	100	98		98	97	96	94
2	108	103	100	96	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	95	91	87	93	89	86		90	87	85		88	85	83	82
4	98	90	85	81	96	89	84	81	87	83	80		85	82	79		83	80	78	76
5	93	85	79	75	91	84	79	75	82	78	74		81	77	73		79	76	73	71
6	88	80	74	70	87	79	74	70	78	73	69		76	72	69		75	71	68	67
7	84	75	69	65	83	74	69	65	73	68	65		72	68	64		71	67	64	63
8	80	71	65	61	79	70	65	61	69	64	61		68	64	60		67	63	60	59
9	76	67	61	57	75	67	61	57	66	61	57		65	60	57		64	60	57	55
10	73	63	58	54	72	63	58	54	62	57	54		61	57	54		61	57	53	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1142330
5°	1112571
10°	1081851
15°	1028274
20°	939532
25°	806803
30°	600334
35°	352456
40°	167965
45°	78424
50°	39068
55°	13676
60°	3158
65°	2452
70°	1587
75°	2097
80°	0
85°	0



TEST NUMBER: P500369

CATALOG NUMBER: LDA2B208030R60D010 2LBDLC1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	211.4	11.0
10°-20°	560.2	29.0
20°-30°	665.1	34.5
30°-40°	375.4	19.5
40°-50°	97.6	5.1
50°-60°	17.8	0.9
60°-70°	1.8	0.1
70°-80°	0.7	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1436.7	74.4
0°-40°	1812.1	93.9
0°-60°	1927.5	99.9
0°-90°	1930.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1930.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2315	
5°	2246	211
15°	2013	560
25°	1482	665
35°	585	375
45°	112	98
55°	16	18
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P500369

CATALOG NUMBER: LDA2B208030R60D010 2LBDLC1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	2315.4
1°	2316.4
2°	2300.5
3°	2286.7
4°	2260.2
5°	2246.5
6°	2222.1
7°	2204.0
8°	2187.1
9°	2175.4
10°	2159.5
11°	2128.8
12°	2100.2
13°	2084.3
14°	2047.1
15°	2013.2
16°	1974.0
17°	1927.3
18°	1882.8
19°	1829.8
20°	1789.5
21°	1734.4
22.5°	1643.2
23°	1627.3
24°	1549.9
25°	1482.1
26°	1406.8
27°	1319.9
28°	1234.0
29°	1150.3
30°	1053.8
32.5°	811.0
35°	585.2
37.5°	399.7
40°	260.8
42.5°	170.7
45°	112.4
47.5°	76.3
50°	50.9
52.5°	31.8
55°	15.9
57.5°	6.4
60°	3.2
62.5°	2.1
65°	2.1



TEST NUMBER: P500369

CATALOG NUMBER: LDA2B208030R60D010 2LBDLC1MMS

CANDELA DISTRIBUTION (continued):

	0°
67.5°	1.1
70°	1.1
72.5°	1.1
75°	1.1
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)