

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P500379

Luminaire Tested: **LDA2B208030R65D010 2LBD1WHH**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P500379
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-66)
Test Lab: INNOVATION CENTER
Issue Date: 3/8/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B208030R65D010 2LBD1WHH
Description: 2000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 3000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1980.2 lumens
Efficiency: N/A
Efficacy: 96.1 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.95
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 20.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P500379

CATALOG NUMBER: LDA2B208030R65D010 2LBD1WHH

Luminous Intensity Polar Plot





TEST NUMBER: P500379

CATALOG NUMBER: LDA2B208030R65D010 2LBD1WHH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	111	108	106	111	109	106	104	104	103	101		101	99	98		97	96	95	93
2	108	103	99	95	106	101	97	94	98	95	92		95	92	90		92	90	88	87
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87	84	82	80
4	97	89	84	79	95	88	83	79	86	82	78		84	80	77		82	79	76	75
5	92	83	78	73	90	82	77	73	81	76	72		79	75	72		77	74	71	69
6	87	78	72	68	86	77	72	67	76	71	67		74	70	66		73	69	66	65
7	83	73	67	63	81	73	67	63	71	66	62		70	65	62		69	65	62	60
8	78	69	63	58	77	68	62	58	67	62	58		66	61	58		65	61	58	56
9	75	65	59	55	73	64	58	54	63	58	54		62	58	54		61	57	54	53
10	71	61	55	51	70	61	55	51	60	55	51		59	54	51		58	54	51	49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1075923
5°	989453
10°	945536
15°	908090
20°	836364
25°	774576
30°	709771
35°	521276
40°	246860
45°	81214
50°	26250
55°	3355
60°	1973
65°	1167
70°	1442
75°	0
80°	0
85°	0



TEST NUMBER: P500379

CATALOG NUMBER: LDA2B208030R65D010 2LBD1WHH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	187.7	9.5
10°-20°	494.4	25.0
20°-30°	655.9	33.1
30°-40°	518.9	26.2
40°-50°	113.4	5.7
50°-60°	8.4	0.4
60°-70°	1.1	0.1
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1338.0	67.6
0°-40°	1856.9	93.8
0°-60°	1978.7	99.9
0°-90°	1980.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1980.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2181	
5°	1998	188
15°	1778	494
25°	1423	656
35°	866	519
45°	116	113
55°	4	8
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P500379

CATALOG NUMBER: LDA2B208030R65D010 2LBD1WHH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2180.8
1°	2169.0
2°	2128.9
3°	2084.9
4°	2039.0
5°	1997.9
6°	1971.5
7°	1945.1
8°	1927.5
9°	1901.1
10°	1887.4
11°	1865.9
12°	1841.4
13°	1819.9
14°	1795.5
15°	1777.9
16°	1732.9
17°	1710.4
18°	1673.2
19°	1639.0
20°	1593.0
21°	1555.9
22.5°	1507.0
23°	1493.3
24°	1456.1
25°	1422.9
26°	1402.3
27°	1368.1
28°	1334.9
29°	1294.8
30°	1245.9
32.5°	1075.7
35°	865.5
37.5°	617.1
40°	383.3
42.5°	216.1
45°	116.4
47.5°	62.6
50°	34.2
52.5°	14.7
55°	3.9
57.5°	2.0
60°	2.0
62.5°	1.0
65°	1.0



TEST NUMBER: P500379

CATALOG NUMBER: LDA2B208030R65D010 2LBD1WHH

CANDELA DISTRIBUTION (continued):

	0°
67.5°	1.0
70°	1.0
72.5°	1.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)