

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P500400

Luminaire Tested: **LDA2B208030R70D010 2LBD1MW**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P500400
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-79)
Test Lab: INNOVATION CENTER
Issue Date: 3/8/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B208030R70D010 2LBD1MW
Description: 2000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 3000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1917.7 lumens
Efficiency: N/A
Efficacy: 93.1 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.09
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 20.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P500400
CATALOG NUMBER: LDA2B208030R70D010 2LBD1MW

Luminous Intensity Polar Plot





TEST NUMBER: P500400

CATALOG NUMBER: LDA2B208030R70D010 2LBD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97	96	95	93
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91	89	87	85
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		85	82	80	78
4	95	87	81	77	93	86	81	76	84	79	75		82	78	74		80	76	74	72
5	90	81	75	70	88	80	74	70	78	73	69		76	72	68		75	71	68	66
6	85	75	69	64	83	74	68	64	73	67	63		71	67	63		70	66	62	61
7	80	70	63	59	79	69	63	59	68	62	58		67	62	58		66	61	58	56
8	76	65	59	54	74	65	59	54	64	58	54		62	57	54		61	57	54	52
9	71	61	55	50	70	61	54	50	60	54	50		59	54	50		58	53	50	48
10	68	57	51	47	67	57	51	47	56	50	47		55	50	46		54	50	46	45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	749269
5°	740988
10°	737332
15°	734736
20°	708521
25°	679258
30°	672456
35°	574277
40°	358343
45°	165778
50°	60021
55°	4215
60°	1973
65°	2335
70°	1442
75°	1906
80°	0
85°	0



TEST NUMBER: P500400

CATALOG NUMBER: LDA2B208030R70D010 2LBD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	141.9	7.4
10°-20°	402.9	21.0
20°-30°	579.3	30.2
30°-40°	571.0	29.8
40°-50°	203.5	10.6
50°-60°	16.7	0.9
60°-70°	1.6	0.1
70°-80°	0.7	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1124.2	58.6
0°-40°	1695.2	88.4
0°-60°	1915.4	99.9
0°-90°	1917.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1917.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1519	
5°	1496	142
15°	1438	403
25°	1248	579
35°	954	571
45°	238	203
55°	5	17
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P500400

CATALOG NUMBER: LDA2B208030R70D010 2LBD1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1518.7
1°	1518.7
2°	1515.8
3°	1516.8
4°	1504.1
5°	1496.2
6°	1485.5
7°	1481.6
8°	1476.7
9°	1475.7
10°	1471.8
11°	1466.9
12°	1466.9
13°	1458.1
14°	1446.4
15°	1438.5
16°	1422.9
17°	1414.1
18°	1386.7
19°	1368.1
20°	1349.5
21°	1325.1
22.5°	1290.9
23°	1277.2
24°	1264.5
25°	1247.8
26°	1238.1
27°	1221.4
28°	1219.5
29°	1201.9
30°	1180.4
32.5°	1097.2
35°	953.5
37.5°	766.7
40°	556.4
42.5°	380.4
45°	237.6
47.5°	141.8
50°	78.2
52.5°	29.3
55°	4.9
57.5°	2.9
60°	2.0
62.5°	2.0
65°	2.0



TEST NUMBER: P500400

CATALOG NUMBER: LDA2B208030R70D010 2LBD1MW

CANDELA DISTRIBUTION (continued):

	0°
67.5°	1.0
70°	1.0
72.5°	1.0
75°	1.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)