

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P500416

Luminaire Tested: **LDA2B208030R70D010 2LBDLC1MW**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P500416  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-81)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B208030R70D010 2LBDLC1MW  
Description: 2000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 3000K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1917.7 lumens  
Efficiency: N/A  
Efficacy: 93.1 lumens/watt  
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 20.6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P500416

CATALOG NUMBER: LDA2B208030R70D010 2LBDLC1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P500416

CATALOG NUMBER: LDA2B208030R70D010 2LBDLC1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	105	111	108	106	103	104	102	100		100	99	97		97	96	94	93
2	107	102	97	94	105	100	96	93	97	93	91		94	91	89		91	89	87	85
3	101	94	89	84	99	93	88	84	90	86	82		87	84	81		85	82	80	78
4	95	87	81	76	93	86	80	76	84	79	75		82	77	74		80	76	73	72
5	90	81	74	70	88	80	74	69	78	73	69		76	72	68		74	71	67	66
6	85	75	68	64	83	74	68	63	72	67	63		71	66	63		70	65	62	61
7	80	70	63	59	78	69	63	58	68	62	58		66	61	58		65	61	57	56
8	75	65	58	54	74	64	58	54	63	58	54		62	57	53		61	57	53	52
9	71	61	54	50	70	60	54	50	59	54	50		58	53	50		57	53	49	48
10	68	57	51	46	66	57	50	46	56	50	46		55	50	46		54	49	46	45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	759234
5°	754805
10°	749756
15°	735860
20°	709256
25°	679040
30°	646820
35°	533744
40°	346943
45°	181267
50°	84275
55°	30879
60°	3158
65°	2452
70°	1587
75°	2097
80°	0
85°	0



TEST NUMBER: P500416

CATALOG NUMBER: LDA2B208030R70D010 2LBDLC1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	144.1	7.5
10°-20°	404.9	21.1
20°-30°	574.6	30.0
30°-40°	537.3	28.0
40°-50°	216.1	11.3
50°-60°	37.8	2.0
60°-70°	1.8	0.1
70°-80°	1.0	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1123.6	58.6
0°-40°	1661.0	86.6
0°-60°	1914.9	99.9
0°-90°	1917.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1917.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1539	
5°	1524	144
15°	1441	405
25°	1247	575
35°	886	537
45°	260	216
55°	36	38
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P500416

CATALOG NUMBER: LDA2B208030R70D010 2LBDLC1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1538.9
1°	1541.0
2°	1537.8
3°	1531.5
4°	1528.3
5°	1524.1
6°	1507.2
7°	1512.5
8°	1497.7
9°	1494.5
10°	1496.6
11°	1482.9
12°	1479.7
13°	1462.8
14°	1456.5
15°	1440.7
16°	1431.1
17°	1412.1
18°	1390.0
19°	1377.3
20°	1350.9
21°	1330.8
22.5°	1293.8
23°	1284.3
24°	1266.4
25°	1247.4
26°	1232.6
27°	1211.5
28°	1190.3
29°	1165.0
30°	1135.4
32.5°	1031.9
35°	886.2
37.5°	714.0
40°	538.7
42.5°	384.5
45°	259.8
47.5°	171.1
50°	109.8
52.5°	68.7
55°	35.9
57.5°	11.6
60°	3.2
62.5°	2.1
65°	2.1



TEST NUMBER: P500416

CATALOG NUMBER: LDA2B208030R70D010 2LBDLC1MW

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	1.1
70°	1.1
72.5°	1.1
75°	1.1
77.5°	1.1
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)