

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P279758

Luminaire Tested: **LDA2B159027D010 EU2B15FL409027 2LBALD1WMH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P279758
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-3)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B159027D010 EU2B15FL409027 2LBALD1WMH
Description: PORTFOLIO 2IN ADJ 1500 LUMEN LED LUMINAIRE WITH FLOOD OPTIC AND 2in
ADJ spun Refl w/lens Self-Flanged, WMH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1173.4 lumens
Efficiency: N/A
Efficacy: 83.2 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.55
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P279758

CATALOG NUMBER: LDA2B159027D010 EU2B15FL409027 2LBALD1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P279758

CATALOG NUMBER: LDA2B159027D010 EU2B15FL409027 2LBALD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																			
3	107	102	98	95	105	101	97	94	98	95	93	96	94	92	94	92	90	89																			
4	103	98	93	90	102	97	93	90	95	91	89	93	90	88	91	89	87	85																			
5	100	94	89	86	98	93	89	86	91	88	85	90	87	84	88	86	83	82																			
6	97	90	85	82	95	89	85	82	88	84	82	87	83	81	85	83	80	79																			
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																			
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																			
9	88	81	76	73	87	80	76	73	79	76	73	79	75	73	78	75	73	72																			
10	85	78	74	71	84	78	74	71	77	73	71	76	73	70	76	72	70	69																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1613540
5°	1579390
10°	1439495
15°	1124553
20°	665784
25°	247523
30°	77363
35°	34390
40°	15972
45°	7535
50°	4145
55°	2322
60°	1085
65°	584
70°	721
75°	0
80°	0
85°	0



TEST NUMBER: P279758

CATALOG NUMBER: LDA2B159027D010 EU2B15FL409027 2LBALD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	294.8	25.1
10°-20°	586.2	50.0
20°-30°	240.1	20.5
30°-40°	39.7	3.4
40°-50°	9.4	0.8
50°-60°	2.5	0.2
60°-70°	0.6	0.0
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1121.1	95.5
0°-40°	1160.9	98.9
0°-60°	1172.8	99.9
0°-90°	1173.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1173.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3270	
5°	3189	295
15°	2202	586
25°	455	240
35°	57	40
45°	11	9
55°	3	3
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P279758

CATALOG NUMBER: LDA2B159027D010 EU2B15FL409027 2LBALD1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3270.5
1°	3259.2
2°	3244.1
3°	3230.6
4°	3212.8
5°	3189.1
6°	3154.1
7°	3108.3
8°	3043.1
9°	2963.9
10°	2873.4
11°	2768.4
12°	2649.9
13°	2514.7
14°	2364.4
15°	2201.7
17.5°	1745.9
20°	1268.1
22.5°	811.8
25°	454.7
27.5°	239.7
30°	135.8
32.5°	86.2
35°	57.1
37.5°	37.7
40°	24.8
42.5°	16.2
45°	10.8
47.5°	7.5
50°	5.4
52.5°	3.8
55°	2.7
57.5°	1.6
60°	1.1
62.5°	0.5
65°	0.5
67.5°	0.5
70°	0.5
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P279758

CATALOG NUMBER: LDA2B159027D010 EU2B15FL409027 2LBALD1WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)