

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P280649

Luminaire Tested: **LDA2B159027D010 EU2B15WFL559027 2LBAD1GPH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P280649
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-5)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B159027D010 EU2B15WFL559027 2LBAD1GPH
Description: PORTFOLIO 2IN ADJ 1500 LUMEN LED LUMINAIRE WITH WIDE FLOOD OPTIC AND
2in ADJ spun Refl, Self-Flanged, GPH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1180.7 lumens
Efficiency: N/A
Efficacy: 83.7 lumens/watt
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.73
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P280649

CATALOG NUMBER: LDA2B159027D010 EU2B15WFL559027 2LBAD1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P280649

CATALOG NUMBER: LDA2B159027D010 EU2B15WFL559027 2LBAD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	109	107	112	110	108	106	106	104	103	102	101	99	98	97	97	95
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	90
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	88	86	85
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	80
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76
6	92	84	79	75	91	84	79	75	82	78	75	81	77	74	80	76	74	72
7	88	80	75	71	87	80	75	71	78	74	71	77	73	70	76	73	70	69
8	85	76	71	68	84	76	71	67	75	70	67	74	70	67	73	69	67	65
9	81	73	68	64	80	72	68	64	72	67	64	71	67	64	70	66	64	62
10	78	70	65	61	77	69	64	61	69	64	61	68	64	61	67	63	61	59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1008382
5°	987818
10°	918584
15°	802055
20°	664051
25°	507892
30°	277892
35°	102870
40°	35615
45°	16048
50°	7599
55°	3785
60°	1085
65°	584
70°	721
75°	0
80°	0
85°	0



TEST NUMBER: P280649

CATALOG NUMBER: LDA2B159027D010 EU2B15WFL559027 2LBAD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	185.3	15.7
10°-20°	434.0	36.8
20°-30°	410.2	34.7
30°-40°	126.3	10.7
40°-50°	20.0	1.7
50°-60°	4.2	0.4
60°-70°	0.6	0.0
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1029.6	87.2
0°-40°	1155.8	97.9
0°-60°	1180.0	99.9
0°-90°	1180.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1180.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2044	
5°	1995	185
15°	1570	434
25°	933	410
35°	171	126
45°	23	20
55°	4	4
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P280649

CATALOG NUMBER: LDA2B159027D010 EU2B15WFL559027 2LBAD1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2043.9
1°	2036.2
2°	2026.9
3°	2019.2
4°	2009.4
5°	1994.6
6°	1975.4
7°	1949.7
8°	1915.2
9°	1875.2
10°	1833.6
11°	1787.6
12°	1738.9
13°	1685.8
14°	1630.5
15°	1570.3
17.5°	1410.9
20°	1264.8
22.5°	1116.4
25°	933.0
27.5°	711.8
30°	487.8
32.5°	299.5
35°	170.8
37.5°	95.3
40°	55.3
42.5°	34.5
45°	23.0
47.5°	15.3
50°	9.9
52.5°	6.6
55°	4.4
57.5°	2.7
60°	1.1
62.5°	0.5
65°	0.5
67.5°	0.5
70°	0.5
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P280649

CATALOG NUMBER: LDA2B159027D010 EU2B15WFL559027 2LBAD1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)