

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P498989

Luminaire Tested: **LDA2B159035R35D010 2LBD1GPH-30DEG TILT**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P498989
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-28)
Test Lab: INNOVATION CENTER
Issue Date: 3/8/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B159035R35D010 2LBD1GPH-30DEG TILT
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 3500K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 836.4 lumens
Efficiency: N/A
Efficacy: 59.3 lumens/watt
Spacing Criteria (0/90/45): 3.16 / 0.51 / 1.46
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P498989

CATALOG NUMBER: LDA2B159035R35D010 2LBD1GPH-30DEG TILT

Luminous Intensity Polar Plot



— 0°-180° - - - 45°-225° ···· 90°-270°



TEST NUMBER: P498989

CATALOG NUMBER: LDA2B159035R35D010 2LBD1GPH-30DEG TILT

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	112	109	106	103	109	106	104	101	102	100	98	98	97	95	95	94	92					90				
2	104	98	93	89	102	97	92	88	93	89	86	90	87	84	87	85	82					80				
3	97	89	83	77	95	87	82	77	85	80	76	82	78	74	80	76	73					71				
4	90	80	73	68	88	79	72	67	77	71	66	75	70	66	73	68	65					63				
5	83	73	65	60	82	72	65	59	70	63	59	68	62	58	66	61	58					56				
6	77	66	58	53	76	65	58	52	63	57	52	62	56	52	60	55	51					49				
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46					44				
8	67	54	47	42	65	54	46	41	53	46	41	51	45	41	50	45	41					39				
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	36					35				
10	58	46	38	33	57	45	38	33	44	38	33	43	37	33	42	37	33					31				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	13962	13962	13962
5°	43730	12233	7577
10°	186662	10320	5611
15°	603112	7508	4495
20°	1242996	4620	3098
25°	1643491	2232	1905
30°	1762834	1025	1025
35°	1684708	723	361
40°	1572870	386	0
45°	1390205	0	0
50°	987203	461	0
55°	353952	516	0
60°	54566	1184	0
65°	2802	1401	0
70°	0	1731	0
75°	0	2287	1144
80°	0	3409	0
85°	0	6793	0



TEST NUMBER: P498989

CATALOG NUMBER: LDA2B159035R35D010 2LBD1GPH-30DEG TILT

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	5.0	0.6
10°-20°	67.7	8.1
20°-30°	226.6	27.1
30°-40°	285.4	34.1
40°-50°	201.9	24.1
50°-60°	46.6	5.6
60°-70°	1.5	0.2
70°-80°	1.0	0.1
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	299.2	35.8
0°-40°	584.6	69.9
0°-60°	833.1	99.6
0°-90°	836.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	836.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	28	28	28	28	28	
5°	88	58	25	18	15	16
15°	1181	208	15	10	9	389
25°	3019	330	4	4	4	1361
35°	2797	193	1	1	1	1751
45°	1992	48	0	0	0	1494
55°	412	2	1	1	0	466
65°	2	1	1	1	0	9
75°	0	1	1	1	1	0
85°	0	1	1	1	0	0
90°	0	0	0	0	0	



TEST NUMBER: P498989

CATALOG NUMBER: LDA2B159035R35D010 2LBD1GPH-30DEG TILT

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	28.3	28.3	28.3	28.3	28.3	28.3	28.3	28.3	28.3
1°	35.3	34.1	32.4	29.4	26.5	25.3	25.3	23.5	23.5
2°	42.4	40.6	37.1	31.2	26.5	23.5	22.4	21.2	20.6
3°	54.7	50.0	42.4	33.6	25.9	22.4	21.8	18.8	18.8
4°	68.3	63.6	48.9	35.3	25.3	21.2	18.8	17.7	17.1
5°	88.3	77.7	57.7	37.1	24.7	20.0	17.7	15.9	15.3
6°	114.2	99.5	65.9	38.8	24.1	18.8	16.5	14.7	14.1
7°	143.6	123.6	75.9	40.6	23.0	17.7	15.3	14.1	13.5
8°	206.0	158.9	87.7	41.8	22.4	16.5	14.7	12.9	12.4
9°	275.5	205.4	100.7	43.6	21.2	15.9	13.5	12.4	11.8
10°	372.6	269.0	115.4	44.7	20.6	14.7	12.4	11.8	11.2
11°	469.1	347.9	133.6	45.3	19.4	12.9	12.4	11.8	11.2
12°	628.1	423.2	149.5	45.3	18.2	12.4	11.2	10.6	10.0
13°	816.4	552.7	172.5	45.9	16.5	11.8	10.6	10.0	10.0
14°	982.4	668.7	187.8	45.9	15.9	10.6	10.0	10.0	9.4
15°	1180.8	781.7	208.4	45.3	14.7	10.0	10.0	9.4	8.8
16°	1388.6	951.2	236.0	44.1	13.5	8.8	9.4	8.2	7.7
17°	1664.1	1091.3	257.2	43.0	12.4	8.2	8.2	8.2	7.7
18°	1916.0	1261.4	274.3	41.8	11.2	8.2	7.7	7.7	7.1
19°	2186.2	1398.0	291.4	40.0	10.0	7.1	7.1	7.1	6.5
20°	2367.5	1565.8	310.2	38.3	8.8	6.5	7.1	6.5	5.9
21°	2597.0	1715.9	317.3	36.5	7.7	5.9	5.9	5.9	5.3
22.5°	2811.9	1915.4	328.5	33.0	6.5	4.7	5.3	4.7	4.7
23°	2844.8	1957.8	328.5	31.8	5.9	4.7	5.3	4.7	4.7
24°	2954.3	2073.7	332.6	29.4	4.7	4.1	4.7	4.1	4.1
25°	3019.1	2165.6	329.6	27.1	4.1	4.1	4.1	4.1	3.5
26°	3045.6	2190.9	322.6	25.3	3.5	3.5	4.1	3.5	2.9
27°	3073.2	2248.6	313.7	23.0	2.9	3.5	3.5	3.5	2.9
28°	3092.7	2255.6	304.9	21.2	2.4	2.9	3.5	2.9	2.9
29°	3099.1	2265.0	294.3	18.8	1.8	2.4	2.9	2.4	2.4
30°	3094.4	2263.3	279.0	17.1	1.8	2.4	2.4	2.4	1.8
32.5°	3004.4	2212.7	236.6	12.4	1.2	1.8	1.8	1.8	1.2
35°	2797.2	2096.1	193.1	8.2	1.2	1.2	1.2	1.2	0.6
37.5°	2633.5	1921.9	147.7	4.7	0.6	1.2	1.2	0.6	0.0
40°	2442.2	1669.3	106.5	2.9	0.6	0.6	0.6	0.0	0.0
42.5°	2248.0	1412.1	72.4	1.2	0.0	0.6	0.6	0.0	0.0
45°	1992.5	1081.3	47.7	0.6	0.0	0.6	0.0	0.0	0.0
47.5°	1675.8	785.2	32.4	0.0	0.0	0.6	0.0	0.0	0.0
50°	1286.2	439.7	18.2	0.0	0.6	0.6	0.6	0.0	0.0
52.5°	847.6	219.6	7.1	0.0	0.6	0.6	0.6	0.0	0.0
55°	411.5	117.7	2.4	0.6	0.6	1.2	0.6	0.0	0.0
57.5°	194.2	45.9	0.6	0.6	1.2	1.2	0.6	0.0	0.0
60°	55.3	9.4	0.6	0.6	1.2	1.2	0.6	0.6	0.0
62.5°	7.7	1.2	0.6	1.2	1.2	1.2	1.2	0.6	0.0
65°	2.4	0.6	0.6	1.2	1.2	1.2	1.2	0.6	0.0



TEST NUMBER: P498989

CATALOG NUMBER: LDA2B159035R35D010 2LBD1GPH-30DEG TILT

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
67.5°	0.6	0.6	0.6	1.2	1.2	1.2	1.2	0.6	0.0
70°	0.0	0.6	0.6	1.2	1.2	1.2	1.2	0.6	0.0
72.5°	0.0	0.6	1.2	1.2	1.2	1.2	1.2	0.6	0.0
75°	0.0	0.6	1.2	1.2	1.2	1.2	1.2	0.6	0.6
77.5°	0.0	0.6	1.2	1.2	1.8	1.2	1.2	0.6	0.0
80°	0.0	0.6	1.2	1.2	1.2	1.2	1.2	0.6	0.0
82.5°	0.0	0.6	1.2	1.2	1.2	1.2	1.2	0.6	0.0
85°	0.0	0.6	1.2	1.2	1.2	1.2	1.2	0.6	0.0
87.5°	0.0	0.6	1.2	1.2	1.2	1.2	0.6	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)