

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P499011

Luminaire Tested: **LDA2B159035R35D010 2LBDC1MW**

Issue Date: 3/12/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P499011
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-27)
Test Lab: INNOVATION CENTER
Issue Date: 3/12/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B159035R35D010 2LBDC1MW
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 3500K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1201.0 lumens
Efficiency: N/A
Efficacy: 85.2 lumens/watt
Spacing Criteria (0/90/45): 0.55 / 0.55 / 0.5
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P499011

CATALOG NUMBER: LDA2B159035R35D010 2LBDC1MW

Luminous Intensity Polar Plot





TEST NUMBER: P499011

CATALOG NUMBER: LDA2B159035R35D010 2LBDC1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	
1	115	113	111	109	112	111	109	107	107	105	104	103	102	101	100	99	98	96	96	96	96	
2	111	107	104	101	109	106	103	100	102	100	98	100	98	96	97	95	94	93	93	93	93	
3	107	102	99	96	105	101	98	95	99	96	93	96	94	92	94	92	91	89	89	89	89	
4	104	98	94	91	102	97	93	90	95	92	89	93	90	88	91	89	87	86	86	86	86	
5	100	94	90	87	99	93	89	86	92	88	86	90	87	85	89	86	84	83	83	83	83	
6	97	91	86	83	96	90	86	83	89	85	82	87	84	82	86	83	81	80	80	80	80	
7	94	87	83	80	93	87	83	80	86	82	79	85	81	79	84	81	79	78	78	78	78	
8	91	84	80	77	90	84	80	77	83	79	77	82	79	76	81	78	76	75	75	75	75	
9	89	82	77	75	88	81	77	74	80	77	74	80	76	74	79	76	74	73	73	73	73	
10	86	79	75	72	85	79	75	72	78	74	72	77	74	72	77	74	72	71	71	71	71	

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1887356
5°	1815573
10°	1644293
15°	1144575
20°	560936
25°	209254
30°	91890
35°	44689
40°	20480
45°	11094
50°	5449
55°	1548
60°	592
65°	700
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P499011

CATALOG NUMBER: LDA2B159035R35D010 2LBDC1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	338.7	28.2
10°-20°	593.7	49.4
20°-30°	202.3	16.8
30°-40°	50.3	4.2
40°-50°	13.0	1.1
50°-60°	2.4	0.2
60°-70°	0.5	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1134.8	94.5
0°-40°	1185.1	98.7
0°-60°	1200.5	100.0
0°-90°	1201.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1201.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3826	
5°	3666	339
15°	2241	594
25°	384	202
35°	74	50
45°	16	13
55°	2	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P499011

CATALOG NUMBER: LDA2B159035R35D010 2LBDC1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	3825.5
1°	3817.9
2°	3788.4
3°	3760.2
4°	3714.8
5°	3666.0
6°	3618.3
7°	3573.6
8°	3477.0
9°	3383.5
10°	3282.2
11°	3116.2
12°	2936.1
13°	2704.2
14°	2489.3
15°	2240.9
16°	1998.4
17°	1745.9
18°	1509.8
19°	1270.9
20°	1068.4
21°	875.3
22.5°	642.2
23°	576.9
24°	470.9
25°	384.4
26°	317.9
27°	265.5
28°	223.7
29°	189.0
30°	161.3
32.5°	109.5
35°	74.2
37.5°	50.0
40°	31.8
42.5°	21.8
45°	15.9
47.5°	11.2
50°	7.1
52.5°	4.1
55°	1.8
57.5°	1.2
60°	0.6
62.5°	0.6
65°	0.6



TEST NUMBER: P499011

CATALOG NUMBER: LDA2B159035R35D010 2LBDC1MW

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.6
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)