

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P499025

Luminaire Tested: **LDA2B159035R35D010 2LBDLC1MMS**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P499025
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-29)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B159035R35D010 2LBDLC1MMS
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 3500K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1201.0 lumens
Efficiency: N/A
Efficacy: 85.2 lumens/watt
Spacing Criteria (0/90/45): 0.54 / 0.54 / 0.51
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P499025

CATALOG NUMBER: LDA2B159035R35D010 2LBDLC1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P499025

CATALOG NUMBER: LDA2B159035R35D010 2LBDLC1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	115	113	111	109	112	110	109	107	106	105	104		103	102	101		99	99	98	96
2	111	107	104	101	109	105	102	100	102	100	98		99	97	96		97	95	94	92
3	107	102	98	95	105	101	97	94	98	95	93		96	93	91		94	92	90	89
4	103	97	93	90	102	96	92	89	94	91	88		92	90	87		91	88	87	85
5	100	93	89	86	98	93	88	85	91	87	85		89	86	84		88	85	83	82
6	96	90	85	82	95	89	85	82	88	84	81		86	83	81		85	82	80	79
7	93	86	82	79	92	86	82	79	85	81	78		84	80	78		83	80	77	76
8	90	83	79	76	89	83	79	76	82	78	75		81	78	75		80	77	75	74
9	88	81	76	73	87	80	76	73	79	76	73		79	75	73		78	75	72	71
10	85	78	74	71	84	78	73	71	77	73	70		76	73	70		76	72	70	69

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1832987
5°	1772140
10°	1548657
15°	1082670
20°	568497
25°	244256
30°	111715
35°	54145
40°	27500
45°	14024
50°	7752
55°	3269
60°	1283
65°	700
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P499025

CATALOG NUMBER: LDA2B159035R35D010 2LBDLC1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	326.2	27.2
10°-20°	565.6	47.1
20°-30°	225.7	18.8
30°-40°	61.6	5.1
40°-50°	17.1	1.4
50°-60°	4.0	0.3
60°-70°	0.8	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1117.6	93.1
0°-40°	1179.1	98.2
0°-60°	1200.2	99.9
0°-90°	1201.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1201.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3715	
5°	3578	326
15°	2120	566
25°	449	226
35°	90	62
45°	20	17
55°	4	4
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P499025

CATALOG NUMBER: LDA2B159035R35D010 2LBDLC1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	3715.3
1°	3699.6
2°	3684.5
3°	3661.9
4°	3628.0
5°	3578.3
6°	3513.6
7°	3433.1
8°	3341.4
9°	3214.4
10°	3091.3
11°	2938.6
12°	2743.1
13°	2546.4
14°	2346.0
15°	2119.7
16°	1897.2
17°	1668.5
18°	1463.0
19°	1268.8
20°	1082.8
21°	911.9
22.5°	707.0
23°	641.0
24°	537.9
25°	448.7
26°	377.7
27°	315.5
28°	267.1
29°	227.5
30°	196.1
32.5°	131.3
35°	89.9
37.5°	62.8
40°	42.7
42.5°	28.9
45°	20.1
47.5°	14.5
50°	10.1
52.5°	6.9
55°	3.8
57.5°	1.9
60°	1.3
62.5°	1.3
65°	0.6



TEST NUMBER: P499025

CATALOG NUMBER: LDA2B159035R35D010 2LBDLC1MMS

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.6
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)