

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P499042

Luminaire Tested: **LDA2B159035R45D010 2LBDL1LI**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P499042  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-42)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B159035R45D010 2LBDL1LI  
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 3500K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1136.9 lumens  
Efficiency: N/A  
Efficacy: 80.6 lumens/watt  
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.65  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 14.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P499042  
CATALOG NUMBER: LDA2B159035R45D010 2LBDL1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P499042

CATALOG NUMBER: LDA2B159035R45D010 2LBDL1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |     |     |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  | 0   |     |     |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 | 102 | 102 | 100 |
| 1   | 114 | 112 | 110 | 108 | 112 | 110 | 108 | 106 | 106 | 104 | 103 |  | 102 | 101 | 100 |  | 99  | 98  | 97  | 95  |
| 2   | 110 | 105 | 102 | 99  | 108 | 104 | 101 | 98  | 101 | 98  | 96  |  | 98  | 96  | 94  |  | 95  | 93  | 92  | 90  |
| 3   | 105 | 100 | 96  | 92  | 103 | 98  | 95  | 91  | 96  | 93  | 90  |  | 94  | 91  | 89  |  | 91  | 89  | 87  | 86  |
| 4   | 101 | 95  | 90  | 86  | 99  | 94  | 89  | 86  | 91  | 88  | 85  |  | 90  | 86  | 84  |  | 88  | 85  | 83  | 82  |
| 5   | 97  | 90  | 85  | 81  | 95  | 89  | 84  | 81  | 87  | 83  | 80  |  | 86  | 82  | 80  |  | 84  | 81  | 79  | 78  |
| 6   | 93  | 86  | 81  | 77  | 92  | 85  | 80  | 77  | 84  | 79  | 76  |  | 82  | 79  | 76  |  | 81  | 78  | 75  | 74  |
| 7   | 90  | 82  | 77  | 73  | 88  | 81  | 76  | 73  | 80  | 76  | 73  |  | 79  | 75  | 72  |  | 78  | 74  | 72  | 71  |
| 8   | 86  | 78  | 73  | 70  | 85  | 78  | 73  | 70  | 77  | 72  | 69  |  | 76  | 72  | 69  |  | 75  | 71  | 69  | 68  |
| 9   | 83  | 75  | 70  | 66  | 82  | 74  | 70  | 66  | 74  | 69  | 66  |  | 73  | 69  | 66  |  | 72  | 68  | 66  | 65  |
| 10  | 80  | 72  | 67  | 64  | 79  | 71  | 67  | 64  | 71  | 66  | 63  |  | 70  | 66  | 63  |  | 69  | 66  | 63  | 62  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |         |
|-----|---------|
|     | 0°      |
| 0°  | 1126789 |
| 5°  | 1101923 |
| 10° | 1022385 |
| 15° | 871877  |
| 20° | 656438  |
| 25° | 395753  |
| 30° | 190788  |
| 35° | 86488   |
| 40° | 39802   |
| 45° | 20513   |
| 50° | 10822   |
| 55° | 4043    |
| 60° | 1184    |
| 65° | 700     |
| 70° | 865     |
| 75° | 0       |
| 80° | 0       |
| 85° | 0       |



TEST NUMBER: P499042

CATALOG NUMBER: LDA2B159035R45D010 2LBDL1LI

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 206.9  | 18.2      |
| 10°-20°   | 466.2  | 41.0      |
| 20°-30°   | 333.0  | 29.3      |
| 30°-40°   | 99.8   | 8.8       |
| 40°-50°   | 24.8   | 2.2       |
| 50°-60°   | 5.2    | 0.5       |
| 60°-70°   | 0.8    | 0.1       |
| 70°-80°   | 0.2    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1006.1 | 88.5      |
| 0°-40°    | 1105.9 | 97.3      |
| 0°-60°    | 1135.8 | 99.9      |
| 0°-90°    | 1136.9 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1136.9 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 2284 |      |
| 5°  | 2225 | 207  |
| 15° | 1707 | 466  |
| 25° | 727  | 333  |
| 35° | 144  | 100  |
| 45° | 29   | 25   |
| 55° | 5    | 5    |
| 65° | 1    | 1    |
| 75° | 0    | 0    |
| 85° | 0    | 0    |
| 90° | 0    |      |



TEST NUMBER: P499042

CATALOG NUMBER: LDA2B159035R45D010 2LBDL1LI

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 2283.9 |
| 1°    | 2288.0 |
| 2°    | 2282.7 |
| 3°    | 2263.3 |
| 4°    | 2249.2 |
| 5°    | 2225.0 |
| 6°    | 2200.9 |
| 7°    | 2175.0 |
| 8°    | 2132.6 |
| 9°    | 2092.6 |
| 10°   | 2040.8 |
| 11°   | 1989.0 |
| 12°   | 1923.6 |
| 13°   | 1853.6 |
| 14°   | 1788.3 |
| 15°   | 1707.0 |
| 16°   | 1627.6 |
| 17°   | 1537.5 |
| 18°   | 1452.2 |
| 19°   | 1347.4 |
| 20°   | 1250.3 |
| 21°   | 1142.5 |
| 22.5° | 981.8  |
| 23°   | 927.7  |
| 24°   | 822.3  |
| 25°   | 727.0  |
| 26°   | 631.6  |
| 27°   | 544.5  |
| 28°   | 463.3  |
| 29°   | 396.7  |
| 30°   | 334.9  |
| 32.5° | 220.1  |
| 35°   | 143.6  |
| 37.5° | 94.2   |
| 40°   | 61.8   |
| 42.5° | 41.8   |
| 45°   | 29.4   |
| 47.5° | 21.2   |
| 50°   | 14.1   |
| 52.5° | 8.8    |
| 55°   | 4.7    |
| 57.5° | 2.4    |
| 60°   | 1.2    |
| 62.5° | 1.2    |
| 65°   | 0.6    |



TEST NUMBER: P499042

CATALOG NUMBER: LDA2B159035R45D010 2LBDL1LI

**CANDELA DISTRIBUTION (continued):**

|       | 0°  |
|-------|-----|
| 67.5° | 0.6 |
| 70°   | 0.6 |
| 72.5° | 0.6 |
| 75°   | 0.0 |
| 77.5° | 0.0 |
| 80°   | 0.0 |
| 82.5° | 0.0 |
| 85°   | 0.0 |
| 87.5° | 0.0 |
| 90°   | 0.0 |

(END OF REPORT)