

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P499060

Luminaire Tested: **LDA2B159035R60D010 2LBD1WHH**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P499060  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-53)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/8/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B159035R60D010 2LBD1WHH  
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 3500K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1161.8 lumens  
Efficiency: N/A  
Efficacy: 82.4 lumens/watt  
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.87  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 14.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P499060  
CATALOG NUMBER: LDA2B159035R60D010 2LBD1WHH

### Luminous Intensity Polar Plot





TEST NUMBER: P499060

CATALOG NUMBER: LDA2B159035R60D010 2LBD1WHH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88
3	103	97	92	88	101	96	91	88	93	89	86	91	87	85	88	86	84	82
4	98	91	86	81	96	90	85	81	88	83	80	86	82	79	84	81	78	77
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72
6	89	80	74	70	87	79	74	70	78	73	70	77	72	69	75	72	69	67
7	85	76	70	66	83	75	69	66	74	69	65	73	68	65	71	67	64	63
8	81	71	66	62	79	71	65	61	70	65	61	69	64	61	68	64	61	59
9	77	68	62	58	76	67	62	58	66	61	58	65	61	57	64	60	57	56
10	73	64	58	55	72	64	58	54	63	58	54	62	57	54	61	57	54	53

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	695541
5°	660262
10°	646405
15°	625637
20°	572067
25°	507892
30°	379923
35°	214473
40°	80762
45°	36142
50°	17653
55°	3527
60°	1184
65°	700
70°	865
75°	0
80°	0
85°	0



TEST NUMBER: P499060

CATALOG NUMBER: LDA2B159035R60D010 2LBD1WHH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	126.2	10.9
10°-20°	340.2	29.3
20°-30°	415.7	35.8
30°-40°	226.7	19.5
40°-50°	45.4	3.9
50°-60°	6.5	0.6
60°-70°	0.8	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	882.1	75.9
0°-40°	1108.8	95.4
0°-60°	1160.7	99.9
0°-90°	1161.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1161.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1410	
5°	1333	126
15°	1225	340
25°	933	416
35°	356	227
45°	52	45
55°	4	7
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P499060

CATALOG NUMBER: LDA2B159035R60D010 2LBD1WHH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1409.8
1°	1403.3
2°	1390.9
3°	1374.5
4°	1350.9
5°	1333.2
6°	1323.8
7°	1312.6
8°	1303.8
9°	1299.7
10°	1290.3
11°	1279.7
12°	1270.3
13°	1259.1
14°	1242.6
15°	1224.9
16°	1202.6
17°	1171.4
18°	1151.4
19°	1119.0
20°	1089.6
21°	1062.5
22.5°	1017.2
23°	998.3
24°	969.5
25°	933.0
26°	886.5
27°	837.6
28°	781.7
29°	728.7
30°	666.9
32.5°	511.5
35°	356.1
37.5°	223.1
40°	125.4
42.5°	78.3
45°	51.8
47.5°	35.3
50°	23.0
52.5°	11.8
55°	4.1
57.5°	1.8
60°	1.2
62.5°	1.2
65°	0.6



TEST NUMBER: P499060

CATALOG NUMBER: LDA2B159035R60D010 2LBD1WHH

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.6
70°	0.6
72.5°	0.6
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)