

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P499074

Luminaire Tested: **LDA2B159035R60D010 2LBDLC1MW**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P499074  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-55)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B159035R60D010 2LBDLC1MW  
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 3500K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1161.7 lumens  
Efficiency: N/A  
Efficacy: 82.4 lumens/watt  
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.86  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 14.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P499074

CATALOG NUMBER: LDA2B159035R60D010 2LBDLC1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P499074

CATALOG NUMBER: LDA2B159035R60D010 2LBDLC1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67
7	84	75	69	65	83	74	69	65	73	68	65	72	68	64	71	67	64	63
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59
9	76	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55
10	73	63	58	54	72	63	58	54	62	57	54	61	57	54	61	57	54	52

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	687598
5°	669672
10°	651164
15°	618946
20°	565504
25°	485628
30°	361351
35°	212124
40°	101114
45°	47166
50°	23487
55°	8257
60°	1875
65°	1518
70°	865
75°	1144
80°	0
85°	0



TEST NUMBER: P499074

CATALOG NUMBER: LDA2B159035R60D010 2LBDLC1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	127.2	11.0
10°-20°	337.2	29.0
20°-30°	400.4	34.5
30°-40°	226.0	19.5
40°-50°	58.7	5.1
50°-60°	10.7	0.9
60°-70°	1.1	0.1
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	864.8	74.4
0°-40°	1090.8	93.9
0°-60°	1160.2	99.9
0°-90°	1161.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1161.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1394	
5°	1352	127
15°	1212	337
25°	892	400
35°	352	226
45°	68	59
55°	10	11
65°	1	1
75°	1	0
85°	0	0
90°	0	



TEST NUMBER: P499074

CATALOG NUMBER: LDA2B159035R60D010 2LBDLC1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1393.7
1°	1394.3
2°	1384.7
3°	1376.4
4°	1360.5
5°	1352.2
6°	1337.5
7°	1326.6
8°	1316.4
9°	1309.4
10°	1299.8
11°	1281.3
12°	1264.1
13°	1254.5
14°	1232.2
15°	1211.8
16°	1188.2
17°	1160.1
18°	1133.3
19°	1101.4
20°	1077.1
21°	1044.0
22.5°	989.1
23°	979.5
24°	932.9
25°	892.1
26°	846.8
27°	794.5
28°	742.8
29°	692.4
30°	634.3
32.5°	488.2
35°	352.2
37.5°	240.6
40°	157.0
42.5°	102.7
45°	67.6
47.5°	45.9
50°	30.6
52.5°	19.1
55°	9.6
57.5°	3.8
60°	1.9
62.5°	1.3
65°	1.3



TEST NUMBER: P499074

CATALOG NUMBER: LDA2B159035R60D010 2LBDLC1MW

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.6
70°	0.6
72.5°	0.6
75°	0.6
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)