

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P500550

Luminaire Tested: **LDA2B208035R45D010 2LBD1WMH**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P500550  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-40)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/8/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B208035R45D010 2LBD1WMH  
Description: 2000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 3500K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2043.7 lumens  
Efficiency: N/A  
Efficacy: 99.2 lumens/watt  
Spacing Criteria (0/90/45): 0.71 / 0.71 / 0.65  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 20.6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P500550

CATALOG NUMBER: LDA2B208035R45D010 2LBD1WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P500550

CATALOG NUMBER: LDA2B208035R45D010 2LBD1WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95
2	110	106	102	99	108	104	101	98	101	98	96	98	96	94	95	94	92	91
3	105	100	96	93	104	99	95	92	96	93	90	94	91	89	92	90	88	86
4	101	95	90	87	100	94	90	86	92	88	85	90	87	84	88	86	84	82
5	97	90	86	82	96	90	85	82	88	84	81	86	83	80	85	82	80	78
6	94	86	81	78	92	86	81	77	84	80	77	83	79	76	82	78	76	75
7	90	82	77	74	89	82	77	74	81	76	73	80	76	73	78	75	73	71
8	87	79	74	71	86	78	74	70	77	73	70	76	73	70	76	72	70	68
9	84	76	71	67	83	75	70	67	74	70	67	73	70	67	73	69	67	66
10	81	73	68	65	80	72	68	64	71	67	64	71	67	64	70	67	64	63

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	2028408
5°	1997428
10°	1864019
15°	1626738
20°	1243836
25°	722317
30°	306434
35°	126841
40°	56031
45°	28955
50°	14430
55°	3441
60°	1973
65°	1167
70°	1442
75°	0
80°	0
85°	0



TEST NUMBER: P500550

CATALOG NUMBER: LDA2B208035R45D010 2LBD1WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	375.3	18.4
10°-20°	868.6	42.5
20°-30°	607.3	29.7
30°-40°	150.4	7.4
40°-50°	34.8	1.7
50°-60°	5.8	0.3
60°-70°	1.1	0.1
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1851.3	90.6
0°-40°	2001.6	97.9
0°-60°	2042.2	99.9
0°-90°	2043.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2043.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4111	
5°	4033	375
15°	3185	869
25°	1327	607
35°	211	150
45°	42	35
55°	4	6
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P500550

CATALOG NUMBER: LDA2B208035R45D010 2LBD1WMH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	4111.4
1°	4102.5
2°	4100.5
3°	4087.6
4°	4051.0
5°	4033.2
6°	3996.7
7°	3944.2
8°	3880.0
9°	3813.7
10°	3720.8
11°	3644.6
12°	3551.7
13°	3431.1
14°	3308.5
15°	3184.9
16°	3048.4
17°	2886.3
18°	2722.1
19°	2553.0
20°	2369.1
21°	2148.6
22.5°	1862.9
23°	1745.2
24°	1533.6
25°	1326.9
26°	1133.1
27°	952.2
28°	793.0
29°	654.6
30°	537.9
32.5°	331.2
35°	210.6
37.5°	136.5
40°	87.0
42.5°	59.3
45°	41.5
47.5°	29.7
50°	18.8
52.5°	9.9
55°	4.0
57.5°	2.0
60°	2.0
62.5°	1.0
65°	1.0



TEST NUMBER: P500550

CATALOG NUMBER: LDA2B208035R45D010 2LBD1WMH

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	1.0
70°	1.0
72.5°	1.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)