

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P499080

Luminaire Tested: **LDA2B159035R65D010 2LBD1MMS**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P499080
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-66)
Test Lab: INNOVATION CENTER
Issue Date: 3/8/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B159035R65D010 2LBD1MMS
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 3500K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1191.9 lumens
Efficiency: N/A
Efficacy: 84.5 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.95
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P499080
CATALOG NUMBER: LDA2B159035R65D010 2LBD1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P499080

CATALOG NUMBER: LDA2B159035R65D010 2LBD1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	111	108	106	111	109	106	104	104	103	101		101	99	98		97	96	95	93
2	108	103	99	95	106	101	97	94	98	95	92		95	92	90		92	90	88	87
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87	84	82	80
4	97	89	84	79	95	88	83	79	86	82	78		84	80	77		82	79	76	75
5	92	83	78	73	90	82	77	73	81	76	72		79	75	72		77	74	71	69
6	87	78	72	68	86	77	72	67	76	71	67		74	70	66		73	69	66	65
7	83	73	67	63	81	73	67	63	71	66	62		70	65	62		69	65	62	60
8	78	69	63	58	77	68	62	58	67	62	58		66	61	58		65	61	58	56
9	75	65	59	55	73	64	58	54	63	58	54		62	58	54		61	57	54	53
10	71	61	55	51	70	61	55	51	60	55	51		59	54	51		58	54	51	49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	647587
5°	595583
10°	569155
15°	546570
20°	503446
25°	466248
30°	427207
35°	313729
40°	148580
45°	48840
50°	15811
55°	2064
60°	1184
65°	700
70°	865
75°	0
80°	0
85°	0



TEST NUMBER: P499080

CATALOG NUMBER: LDA2B159035R65D010 2LBD1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	113.0	9.5
10°-20°	297.6	25.0
20°-30°	394.8	33.1
30°-40°	312.3	26.2
40°-50°	68.2	5.7
50°-60°	5.1	0.4
60°-70°	0.7	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	805.4	67.6
0°-40°	1117.7	93.8
0°-60°	1191.0	99.9
0°-90°	1191.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1191.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1313	
5°	1203	113
15°	1070	298
25°	856	395
35°	521	312
45°	70	68
55°	2	5
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P499080

CATALOG NUMBER: LDA2B159035R65D010 2LBD1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	1312.6
1°	1305.6
2°	1281.4
3°	1255.0
4°	1227.3
5°	1202.6
6°	1186.7
7°	1170.8
8°	1160.2
9°	1144.3
10°	1136.1
11°	1123.1
12°	1108.4
13°	1095.4
14°	1080.7
15°	1070.1
16°	1043.1
17°	1029.5
18°	1007.1
19°	986.5
20°	958.9
21°	936.5
22.5°	907.1
23°	898.8
24°	876.5
25°	856.5
26°	844.1
27°	823.5
28°	803.5
29°	779.3
30°	749.9
32.5°	647.5
35°	520.9
37.5°	371.4
40°	230.7
42.5°	130.1
45°	70.0
47.5°	37.7
50°	20.6
52.5°	8.8
55°	2.4
57.5°	1.2
60°	1.2
62.5°	0.6
65°	0.6



TEST NUMBER: P499080

CATALOG NUMBER: LDA2B159035R65D010 2LBD1MMS

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.6
70°	0.6
72.5°	0.6
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)