

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P500552

Luminaire Tested: **LDA2B208035R45D010 2LBDL1GPH**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P500552  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-42)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B208035R45D010 2LBDL1GPH  
Description: 2000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 3500K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1909.7 lumens  
Efficiency: N/A  
Efficacy: 92.7 lumens/watt  
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.65  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 20.6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P500552

CATALOG NUMBER: LDA2B208035R45D010 2LBDL1GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P500552

CATALOG NUMBER: LDA2B208035R45D010 2LBDL1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99	98	97	95
2	110	105	102	99	108	104	101	98	101	98	96		98	96	94		95	93	92	90
3	105	100	96	92	103	98	95	91	96	93	90		94	91	89		91	89	87	86
4	101	95	90	86	99	94	89	86	91	88	85		90	86	84		88	85	83	82
5	97	90	85	81	95	89	84	81	87	83	80		86	82	80		84	81	79	78
6	93	86	81	77	92	85	80	77	84	79	76		82	79	76		81	78	75	74
7	90	82	77	73	88	81	76	73	80	76	73		79	75	72		78	74	72	71
8	86	78	73	70	85	78	73	70	77	72	69		76	72	69		75	71	69	68
9	83	75	70	66	82	74	70	66	74	69	66		73	69	66		72	68	66	65
10	80	72	67	64	79	71	67	64	71	66	63		70	66	63		69	66	63	62

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1892783
5°	1851033
10°	1717384
15°	1464621
20°	1102657
25°	664723
30°	320505
35°	145331
40°	66851
45°	34467
50°	18191
55°	6795
60°	1973
65°	1167
70°	1442
75°	0
80°	0
85°	0



TEST NUMBER: P500552

CATALOG NUMBER: LDA2B208035R45D010 2LBDL1GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	347.5	18.2
10°-20°	783.0	41.0
20°-30°	559.4	29.3
30°-40°	167.7	8.8
40°-50°	41.6	2.2
50°-60°	8.7	0.5
60°-70°	1.4	0.1
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1690.0	88.5
0°-40°	1857.7	97.3
0°-60°	1907.9	99.9
0°-90°	1909.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1909.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3836	
5°	3738	348
15°	2868	783
25°	1221	559
35°	241	168
45°	49	42
55°	8	9
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P500552

CATALOG NUMBER: LDA2B208035R45D010 2LBDL1GPH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3836.5
1°	3843.4
2°	3834.5
3°	3801.9
4°	3778.1
5°	3737.6
6°	3697.1
7°	3653.6
8°	3582.4
9°	3515.1
10°	3428.1
11°	3341.1
12°	3231.3
13°	3113.7
14°	3003.9
15°	2867.5
16°	2734.0
17°	2582.7
18°	2439.3
19°	2263.3
20°	2100.2
21°	1919.2
22.5°	1649.3
23°	1558.3
24°	1381.3
25°	1221.1
26°	1061.0
27°	914.6
28°	778.2
29°	666.4
30°	562.6
32.5°	369.8
35°	241.3
37.5°	158.2
40°	103.8
42.5°	70.2
45°	49.4
47.5°	35.6
50°	23.7
52.5°	14.8
55°	7.9
57.5°	4.0
60°	2.0
62.5°	2.0
65°	1.0



TEST NUMBER: P500552

CATALOG NUMBER: LDA2B208035R45D010 2LBDL1GPH

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	1.0
70°	1.0
72.5°	1.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)