

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P499112

Luminaire Tested: **LDA2B159035R70D010 2LBDL1MB**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P499112  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-81)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B159035R70D010 2LBDL1MB  
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 3500K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1068.8 lumens  
Efficiency: N/A  
Efficacy: 75.8 lumens/watt  
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 14.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P499112  
CATALOG NUMBER: LDA2B159035R70D010 2LBDL1MB

### Luminous Intensity Polar Plot





TEST NUMBER: P499112

CATALOG NUMBER: LDA2B159035R70D010 2LBDL1MB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	105	111	108	106	103	104	102	100		100	99	97		97	96	94	93
2	107	102	97	94	105	100	96	93	97	93	91		94	91	89		91	89	87	85
3	101	94	89	84	99	93	88	84	90	86	82		87	84	81		85	82	80	78
4	95	87	81	76	93	86	80	76	84	79	75		82	77	74		80	76	73	72
5	90	81	74	70	88	80	74	69	78	73	69		76	72	68		74	71	67	66
6	85	75	68	64	83	74	68	63	72	67	63		71	66	63		70	65	62	61
7	80	70	63	59	78	69	63	58	68	62	58		66	61	58		65	61	57	56
8	75	65	58	54	74	64	58	54	63	58	54		62	57	53		61	57	53	52
9	71	61	54	50	70	60	54	50	59	54	50		58	53	50		57	53	49	48
10	68	57	51	46	66	57	50	46	56	50	46		55	50	46		54	49	46	45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	423107
5°	420662
10°	417861
15°	410094
20°	395291
25°	378442
30°	360497
35°	297468
40°	193340
45°	101030
50°	46973
55°	17203
60°	1776
65°	1401
70°	865
75°	1144
80°	0
85°	0



TEST NUMBER: P499112

CATALOG NUMBER: LDA2B159035R70D010 2LBDL1MB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	80.3	7.5
10°-20°	225.6	21.1
20°-30°	320.3	30.0
30°-40°	299.5	28.0
40°-50°	120.5	11.3
50°-60°	21.1	2.0
60°-70°	1.0	0.1
70°-80°	0.6	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	626.2	58.6
0°-40°	925.7	86.6
0°-60°	1067.2	99.9
0°-90°	1068.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1068.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	858	
5°	849	80
15°	803	226
25°	695	320
35°	494	299
45°	145	120
55°	20	21
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P499112

CATALOG NUMBER: LDA2B159035R70D010 2LBDL1MB

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	857.6
1°	858.8
2°	857.0
3°	853.5
4°	851.7
5°	849.4
6°	840.0
7°	842.9
8°	834.7
9°	832.9
10°	834.1
11°	826.4
12°	824.7
13°	815.3
14°	811.7
15°	802.9
16°	797.6
17°	787.0
18°	774.6
19°	767.6
20°	752.9
21°	741.7
22.5°	721.1
23°	715.8
24°	705.8
25°	695.2
26°	686.9
27°	675.2
28°	663.4
29°	649.3
30°	632.8
32.5°	575.1
35°	493.9
37.5°	397.9
40°	300.2
42.5°	214.3
45°	144.8
47.5°	95.4
50°	61.2
52.5°	38.3
55°	20.0
57.5°	6.5
60°	1.8
62.5°	1.2
65°	1.2



TEST NUMBER: P499112

CATALOG NUMBER: LDA2B159035R70D010 2LBDL1MB

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.6
70°	0.6
72.5°	0.6
75°	0.6
77.5°	0.6
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)