

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P500562

Luminaire Tested: **LDA2B208035R45D010 2LBDLC1MMS**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P500562
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-42)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B208035R45D010 2LBDLC1MMS
Description: 2000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 3500K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2043.7 lumens
Efficiency: N/A
Efficacy: 99.2 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.65
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 20.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P500562

CATALOG NUMBER: LDA2B208035R45D010 2LBDLC1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P500562

CATALOG NUMBER: LDA2B208035R45D010 2LBDLC1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95
2	110	105	102	99	108	104	101	98	101	98	96	98	96	94	95	93	92	90
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86
4	101	95	90	86	99	94	89	86	91	88	85	90	86	84	88	85	83	82
5	97	90	85	81	95	89	84	81	87	83	80	86	82	80	84	81	79	78
6	93	86	81	77	92	85	80	77	84	79	76	82	79	76	81	78	75	74
7	90	82	77	73	88	81	76	73	80	76	73	79	75	72	78	74	72	71
8	86	78	73	70	85	78	73	70	77	72	69	76	72	69	75	71	69	68
9	83	75	70	66	82	74	70	66	74	69	66	73	69	66	72	68	66	65
10	80	72	67	64	79	71	67	64	71	66	63	70	66	63	69	66	63	62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2025595
5°	1980936
10°	1837919
15°	1567387
20°	1180045
25°	711376
30°	343007
35°	155510
40°	71553
45°	36909
50°	19495
55°	7311
60°	2072
65°	1284
70°	1587
75°	0
80°	0
85°	0



TEST NUMBER: P500562

CATALOG NUMBER: LDA2B208035R45D010 2LBDLC1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	371.9	18.2
10°-20°	838.0	41.0
20°-30°	598.7	29.3
30°-40°	179.5	8.8
40°-50°	44.5	2.2
50°-60°	9.3	0.5
60°-70°	1.5	0.1
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1808.6	88.5
0°-40°	1988.0	97.3
0°-60°	2041.9	99.9
0°-90°	2043.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2043.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4106	
5°	4000	372
15°	3069	838
25°	1307	599
35°	258	179
45°	53	45
55°	8	9
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P500562

CATALOG NUMBER: LDA2B208035R45D010 2LBDLC1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	4105.7
1°	4113.1
2°	4103.6
3°	4068.7
4°	4043.3
5°	3999.9
6°	3956.5
7°	3910.0
8°	3833.8
9°	3761.8
10°	3668.7
11°	3575.6
12°	3458.1
13°	3332.2
14°	3214.7
15°	3068.7
16°	2925.9
17°	2764.0
18°	2610.5
19°	2422.2
20°	2247.6
21°	2053.9
22.5°	1765.0
23°	1667.7
24°	1478.3
25°	1306.8
26°	1135.4
27°	978.8
28°	832.8
29°	713.2
30°	602.1
32.5°	395.8
35°	258.2
37.5°	169.3
40°	111.1
42.5°	75.1
45°	52.9
47.5°	38.1
50°	25.4
52.5°	15.9
55°	8.5
57.5°	4.2
60°	2.1
62.5°	2.1
65°	1.1



TEST NUMBER: P500562

CATALOG NUMBER: LDA2B208035R45D010 2LBDLC1MMS

CANDELA DISTRIBUTION (continued):

	0°
67.5°	1.1
70°	1.1
72.5°	1.1
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)