

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P500569

Luminaire Tested: **LDA2B208035R60D010 2LBD1MMS**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P500569  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-53)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/8/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B208035R60D010 2LBD1MMS  
Description: 2000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 3500K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1951.5 lumens  
Efficiency: N/A  
Efficacy: 94.7 lumens/watt  
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.87  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 20.6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P500569

CATALOG NUMBER: LDA2B208035R60D010 2LBD1MMS

### Luminous Intensity Polar Plot





TEST NUMBER: P500569

CATALOG NUMBER: LDA2B208035R60D010 2LBD1MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	108	104	100	96	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	96	91	88	93	89	86		91	87	85		88	86	84	82
4	98	91	86	81	96	90	85	81	88	83	80		86	82	79		84	81	78	77
5	93	85	80	75	92	84	79	75	83	78	74		81	77	74		79	76	73	72
6	89	80	74	70	87	79	74	70	78	73	70		77	72	69		75	72	69	67
7	85	76	70	66	83	75	69	66	74	69	65		73	68	65		71	67	64	63
8	81	71	66	62	79	71	65	61	70	65	61		69	64	61		68	64	61	59
9	77	68	62	58	76	67	62	58	66	61	58		65	61	57		64	60	57	56
10	73	64	58	55	72	64	58	54	63	58	54		62	57	54		61	57	54	53

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1168330
5°	1109154
10°	1085808
15°	1051003
20°	960900
25°	853128
30°	638218
35°	360286
40°	135634
45°	60702
50°	29627
55°	5935
60°	1973
65°	1167
70°	1442
75°	0
80°	0
85°	0



TEST NUMBER: P500569

CATALOG NUMBER: LDA2B208035R60D010 2LBD1MMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	212.0	10.9
10°-20°	571.5	29.3
20°-30°	698.2	35.8
30°-40°	380.8	19.5
40°-50°	76.2	3.9
50°-60°	10.9	0.6
60°-70°	1.4	0.1
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1481.8	75.9
0°-40°	1862.6	95.4
0°-60°	1949.7	99.9
0°-90°	1951.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1951.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2368	
5°	2240	212
15°	2058	572
25°	1567	698
35°	598	381
45°	87	76
55°	7	11
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P500569

CATALOG NUMBER: LDA2B208035R60D010 2LBD1MMS

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2368.1
1°	2357.3
2°	2336.5
3°	2308.8
4°	2269.3
5°	2239.6
6°	2223.8
7°	2205.0
8°	2190.1
9°	2183.2
10°	2167.4
11°	2149.6
12°	2133.8
13°	2115.0
14°	2087.3
15°	2057.7
16°	2020.1
17°	1967.7
18°	1934.1
19°	1879.7
20°	1830.2
21°	1784.7
22.5°	1708.6
23°	1677.0
24°	1628.5
25°	1567.2
26°	1489.1
27°	1407.0
28°	1313.1
29°	1224.1
30°	1120.3
32.5°	859.2
35°	598.2
37.5°	374.7
40°	210.6
42.5°	131.5
45°	87.0
47.5°	59.3
50°	38.6
52.5°	19.8
55°	6.9
57.5°	3.0
60°	2.0
62.5°	2.0
65°	1.0



TEST NUMBER: P500569

CATALOG NUMBER: LDA2B208035R60D010 2LBD1MMS

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	1.0
70°	1.0
72.5°	1.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)