

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P279775

Luminaire Tested: **LDA2B159030D010 EU2B15FL409030 2LBALD1WH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P279775
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-3)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B159030D010 EU2B15FL409030 2LBALD1WH
Description: PORTFOLIO 2IN ADJ 1500 LUMEN LED LUMINAIRE WITH FLOOD OPTIC AND 2in
ADJ spun Refl w/lens Self-Flanged, WH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1241.1 lumens
Efficiency: N/A
Efficacy: 88.0 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.55
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P279775

CATALOG NUMBER: LDA2B159030D010 EU2B15FL409030 2LBALD1WH

Luminous Intensity Polar Plot





TEST NUMBER: P279775

CATALOG NUMBER: LDA2B159030D010 EU2B15FL409030 2LBALD1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																												
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																												
3	107	102	98	95	105	101	97	94	98	95	93	96	94	92	94	92	90	89																												
4	103	98	93	90	102	97	93	90	95	91	89	93	90	88	91	89	87	85																												
5	100	94	89	86	98	93	89	86	91	88	85	90	87	84	88	86	83	82																												
6	97	90	85	82	95	89	85	82	88	84	82	87	83	81	85	83	80	79																												
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																												
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																												
9	88	81	76	73	87	80	76	73	79	76	73	79	75	73	78	75	73	72																												
10	85	78	74	71	84	78	74	71	77	73	71	76	73	70	76	72	70	69																												

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1706538
5°	1670466
10°	1522506
15°	1189369
20°	704163
25°	261785
30°	81807
35°	36378
40°	16874
45°	7954
50°	4375
55°	2408
60°	1085
65°	700
70°	865
75°	0
80°	0
85°	0



TEST NUMBER: P279775

CATALOG NUMBER: LDA2B159030D010 EU2B15FL409030 2LBALD1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	311.8	25.1
10°-20°	620.0	50.0
20°-30°	253.9	20.5
30°-40°	42.0	3.4
40°-50°	9.9	0.8
50°-60°	2.6	0.2
60°-70°	0.7	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1185.7	95.5
0°-40°	1227.8	98.9
0°-60°	1240.4	99.9
0°-90°	1241.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1241.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3459	
5°	3373	312
15°	2329	620
25°	481	254
35°	60	42
45°	11	10
55°	3	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P279775

CATALOG NUMBER: LDA2B159030D010 EU2B15FL409030 2LBALD1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3459.0
1°	3447.0
2°	3431.1
3°	3416.8
4°	3398.0
5°	3373.0
6°	3335.9
7°	3287.5
8°	3218.6
9°	3134.8
10°	3039.1
11°	2928.0
12°	2802.6
13°	2659.6
14°	2500.7
15°	2328.6
17.5°	1846.6
20°	1341.2
22.5°	858.6
25°	480.9
27.5°	253.5
30°	143.6
32.5°	91.2
35°	60.4
37.5°	39.9
40°	26.2
42.5°	17.1
45°	11.4
47.5°	8.0
50°	5.7
52.5°	4.0
55°	2.8
57.5°	1.7
60°	1.1
62.5°	0.6
65°	0.6
67.5°	0.6
70°	0.6
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P279775

CATALOG NUMBER: LDA2B159030D010 EU2B15FL409030 2LBALD1WH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)