

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P500583

Luminaire Tested: **LDA2B208035R60D010 2LBDL1WMH**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P500583
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-55)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B208035R60D010 2LBDL1WMH
Description: 2000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 3500K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1800.1 lumens
Efficiency: N/A
Efficacy: 87.4 lumens/watt
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.86
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 20.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P500583

CATALOG NUMBER: LDA2B208035R60D010 2LBDL1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P500583

CATALOG NUMBER: LDA2B208035R60D010 2LBDL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82
4	98	90	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71
6	88	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67
7	84	75	69	65	83	74	69	65	73	68	65	72	68	64	71	67	64	63
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59
9	76	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55
10	73	63	58	54	72	63	58	54	62	57	54	61	57	54	61	57	53	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1065415
5°	1037640
10°	1009009
15°	959065
20°	876319
25°	752475
30°	559887
35°	328726
40°	156630
45°	73121
50°	36458
55°	12730
60°	2960
65°	2335
70°	1442
75°	1906
80°	0
85°	0



TEST NUMBER: P500583

CATALOG NUMBER: LDA2B208035R60D010 2LBDL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	197.2	11.0
10°-20°	522.5	29.0
20°-30°	620.4	34.5
30°-40°	350.1	19.5
40°-50°	91.0	5.1
50°-60°	16.6	0.9
60°-70°	1.7	0.1
70°-80°	0.7	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1340.0	74.4
0°-40°	1690.1	93.9
0°-60°	1797.7	99.9
0°-90°	1800.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1800.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2160	
5°	2095	197
15°	1878	522
25°	1382	620
35°	546	350
45°	105	91
55°	15	17
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P500583

CATALOG NUMBER: LDA2B208035R60D010 2LBDL1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	2159.5
1°	2160.5
2°	2145.7
3°	2132.8
4°	2108.1
5°	2095.2
6°	2072.5
7°	2055.7
8°	2039.9
9°	2029.0
10°	2014.1
11°	1985.5
12°	1958.8
13°	1943.9
14°	1909.3
15°	1877.7
16°	1841.1
17°	1797.6
18°	1756.1
19°	1706.6
20°	1669.1
21°	1617.6
22.5°	1532.6
23°	1517.8
24°	1445.6
25°	1382.3
26°	1312.1
27°	1231.0
28°	1150.9
29°	1072.8
30°	982.8
32.5°	756.4
35°	545.8
37.5°	372.8
40°	243.2
42.5°	159.2
45°	104.8
47.5°	71.2
50°	47.5
52.5°	29.7
55°	14.8
57.5°	5.9
60°	3.0
62.5°	2.0
65°	2.0



TEST NUMBER: P500583

CATALOG NUMBER: LDA2B208035R60D010 2LBDL1WMH

CANDELA DISTRIBUTION (continued):

	0°
67.5°	1.0
70°	1.0
72.5°	1.0
75°	1.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)