

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P500604

Luminaire Tested: **LDA2B208035R65D010 2LBDL1WH**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P500604  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-68)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B208035R65D010 2LBDL1WH  
Description: 2000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 3500K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1850.8 lumens  
Efficiency: N/A  
Efficacy: 89.8 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.94  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 20.6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P500604

CATALOG NUMBER: LDA2B208035R65D010 2LBDL1WH

### Luminous Intensity Polar Plot





TEST NUMBER: P500604

CATALOG NUMBER: LDA2B208035R65D010 2LBDL1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93
2	108	103	99	95	105	101	97	94	98	95	92	95	92	90	92	90	88	87
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80
4	97	89	83	79	95	88	83	79	86	81	78	84	80	77	82	78	76	74
5	92	83	77	73	90	82	76	72	80	75	72	79	74	71	77	73	70	69
6	87	78	72	67	85	77	71	67	75	70	66	74	69	66	73	69	65	64
7	82	73	67	62	81	72	66	62	71	66	62	70	65	61	68	64	61	60
8	78	68	62	58	77	68	62	58	67	61	58	66	61	57	65	60	57	56
9	74	64	58	54	73	64	58	54	63	57	54	62	57	54	61	57	53	52
10	71	61	55	51	70	60	54	51	59	54	50	59	54	50	58	53	50	49

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	968321
5°	927943
10°	883716
15°	839852
20°	781289
25°	721283
30°	625799
35°	449002
40°	243897
45°	104169
50°	44747
55°	16171
60°	2960
65°	2335
70°	1442
75°	0
80°	0
85°	0



TEST NUMBER: P500604

CATALOG NUMBER: LDA2B208035R65D010 2LBDL1WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	175.4	9.5
10°-20°	460.6	24.9
20°-30°	602.2	32.5
30°-40°	458.1	24.8
40°-50°	132.4	7.2
50°-60°	19.9	1.1
60°-70°	1.7	0.1
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1238.2	66.9
0°-40°	1696.4	91.7
0°-60°	1848.7	99.9
0°-90°	1850.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1850.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1963	
5°	1874	175
15°	1644	461
25°	1325	602
35°	746	458
45°	149	132
55°	19	20
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P500604

CATALOG NUMBER: LDA2B208035R65D010 2LBDL1WH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1962.7
1°	1955.8
2°	1944.9
3°	1923.2
4°	1899.4
5°	1873.7
6°	1849.0
7°	1827.3
8°	1806.5
9°	1787.7
10°	1764.0
11°	1743.2
12°	1721.5
13°	1699.7
14°	1676.0
15°	1644.3
16°	1620.6
17°	1591.9
18°	1548.4
19°	1525.7
20°	1488.1
21°	1454.5
22.5°	1403.1
23°	1383.3
24°	1352.7
25°	1325.0
26°	1288.4
27°	1247.8
28°	1203.3
29°	1155.9
30°	1098.5
32.5°	941.3
35°	745.5
37.5°	549.8
40°	378.7
42.5°	240.3
45°	149.3
47.5°	92.9
50°	58.3
52.5°	34.6
55°	18.8
57.5°	6.9
60°	3.0
62.5°	2.0
65°	2.0



TEST NUMBER: P500604

CATALOG NUMBER: LDA2B208035R65D010 2LBDL1WH

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	1.0
70°	1.0
72.5°	1.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)