

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P280666

Luminaire Tested: **LDA2B159030D010 EU2B15WFL559030 2LBALD1LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P280666
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-5)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B159030D010 EU2B15WFL559030 2LBALD1LI
Description: PORTFOLIO 2IN ADJ 1500 LUMEN LED LUMINAIRE WITH WIDE FLOOD OPTIC AND
2in ADJ spun Refl w/lens Self-Flanged, H
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1220.4 lumens
Efficiency: N/A
Efficacy: 86.6 lumens/watt
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.73
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P280666

CATALOG NUMBER: LDA2B159030D010 EU2B15WFL559030 2LBALD1LI

Luminous Intensity Polar Plot





TEST NUMBER: P280666

CATALOG NUMBER: LDA2B159030D010 EU2B15WFL559030 2LBALD1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	112	109	107	112	110	108	106	106	104	103	102	101	99	98	97	97	95		
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	90		
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	88	86	85		
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	80		
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76		
6	92	84	79	75	91	84	79	75	82	78	75	81	77	74	80	76	74	72		
7	88	80	75	71	87	80	75	71	78	74	71	77	73	70	76	73	70	69		
8	85	76	71	68	84	76	71	67	75	70	67	74	70	67	73	69	67	65		
9	81	73	68	64	80	72	68	64	72	67	64	71	67	64	70	66	64	62		
10	78	70	65	61	77	69	64	61	69	64	61	68	64	61	67	63	61	59		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1042276
5°	1021000
10°	949494
15°	828973
20°	686365
25°	524931
30°	287235
35°	106363
40°	36839
45°	16606
50°	7829
55°	3871
60°	1085
65°	700
70°	865
75°	0
80°	0
85°	0



TEST NUMBER: P280666

CATALOG NUMBER: LDA2B159030D010 EU2B15WFL559030 2LBALD1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	191.6	15.7
10°-20°	448.6	36.8
20°-30°	424.0	34.7
30°-40°	130.5	10.7
40°-50°	20.6	1.7
50°-60°	4.4	0.4
60°-70°	0.7	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1064.2	87.2
0°-40°	1194.7	97.9
0°-60°	1219.7	99.9
0°-90°	1220.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1220.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2113	
5°	2062	192
15°	1623	449
25°	964	424
35°	177	131
45°	24	21
55°	4	4
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P280666

CATALOG NUMBER: LDA2B159030D010 EU2B15WFL559030 2LBALD1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	2112.6
1°	2104.6
2°	2095.0
3°	2087.1
4°	2076.9
5°	2061.6
6°	2041.8
7°	2015.2
8°	1979.6
9°	1938.3
10°	1895.3
11°	1847.7
12°	1797.3
13°	1742.5
14°	1685.3
15°	1623.0
17.5°	1458.4
20°	1307.3
22.5°	1153.9
25°	964.3
27.5°	735.7
30°	504.2
32.5°	309.6
35°	176.6
37.5°	98.5
40°	57.2
42.5°	35.7
45°	23.8
47.5°	15.8
50°	10.2
52.5°	6.8
55°	4.5
57.5°	2.8
60°	1.1
62.5°	0.6
65°	0.6
67.5°	0.6
70°	0.6
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P280666

CATALOG NUMBER: LDA2B159030D010 EU2B15WFL559030 2LBALD1LI

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)