

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P499313

Luminaire Tested: **LDA2B159040R65D010 2LBDLC1MW**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P499313
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-68)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B159040R65D010 2LBDLC1MW
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 4000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1217.3 lumens
Efficiency: N/A
Efficacy: 86.3 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.94
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P499313

CATALOG NUMBER: LDA2B159040R65D010 2LBDLC1MW

Luminous Intensity Polar Plot





TEST NUMBER: P499313

CATALOG NUMBER: LDA2B159040R65D010 2LBDLC1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	111	108	106	111	108	106	104	104	103	101		101	99	98		97	96	95	93
2	108	103	99	95	105	101	97	94	98	95	92		95	92	90		92	90	88	87
3	102	95	90	86	100	94	89	86	91	88	84		89	86	83		87	84	82	80
4	97	89	83	79	95	88	83	79	86	81	78		84	80	77		82	78	76	74
5	92	83	77	73	90	82	76	72	80	75	72		79	74	71		77	73	70	69
6	87	78	72	67	85	77	71	67	75	70	66		74	69	66		73	69	65	64
7	82	73	67	62	81	72	66	62	71	66	62		70	65	61		68	64	61	60
8	78	68	62	58	77	68	62	58	67	61	58		66	61	57		65	60	57	56
9	74	64	58	54	73	64	58	54	63	57	54		62	57	54		61	57	53	52
10	71	61	55	51	69	60	54	51	59	54	50		59	54	50		58	53	50	49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	636831
5°	610292
10°	581178
15°	552342
20°	513842
25°	474359
30°	411598
35°	295300
40°	160430
45°	68516
50°	29473
55°	10666
60°	1973
65°	1518
70°	1010
75°	0
80°	0
85°	0



TEST NUMBER: P499313

CATALOG NUMBER: LDA2B159040R65D010 2LBDLC1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.4	9.5
10°-20°	302.9	24.9
20°-30°	396.1	32.5
30°-40°	301.3	24.8
40°-50°	87.1	7.2
50°-60°	13.1	1.1
60°-70°	1.1	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	814.4	66.9
0°-40°	1115.7	91.6
0°-60°	1215.9	99.9
0°-90°	1217.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1217.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1291	
5°	1232	115
15°	1081	303
25°	871	396
35°	490	301
45°	98	87
55°	12	13
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P499313

CATALOG NUMBER: LDA2B159040R65D010 2LBDLC1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1290.8
1°	1286.3
2°	1279.1
3°	1264.8
4°	1249.2
5°	1232.3
6°	1216.0
7°	1201.7
8°	1188.1
9°	1175.7
10°	1160.1
11°	1146.5
12°	1132.2
13°	1117.8
14°	1102.2
15°	1081.4
16°	1065.8
17°	1047.0
18°	1018.4
19°	1003.4
20°	978.7
21°	956.6
22.5°	922.8
23°	909.8
24°	889.6
25°	871.4
26°	847.3
27°	820.7
28°	791.4
29°	760.2
30°	722.5
32.5°	619.1
35°	490.3
37.5°	361.6
40°	249.1
42.5°	158.0
45°	98.2
47.5°	61.1
50°	38.4
52.5°	22.8
55°	12.4
57.5°	4.6
60°	2.0
62.5°	1.3
65°	1.3



TEST NUMBER: P499313

CATALOG NUMBER: LDA2B159040R65D010 2LBDLC1MW

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.7
70°	0.7
72.5°	0.7
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)