

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P279950

Luminaire Tested: **LDA2B208050D010 EU2B20FL408050 2LBALD1WMH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P279950
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-3)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B208050D010 EU2B20FL408050 2LBALD1WMH
Description: PORTFOLIO 2IN ADJ 2000 LUMEN LED LUMINAIRE WITH FLOOD OPTIC AND 2in
ADJ spun Refl w/lens Self-Flanged, WMH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2207.7 lumens
Efficiency: N/A
Efficacy: 107.2 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.55
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P279950

CATALOG NUMBER: LDA2B208050D010 EU2B20FL408050 2LBALD1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P279950

CATALOG NUMBER: LDA2B208050D010 EU2B20FL408050 2LBALD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92
3	107	102	98	95	105	101	97	94	98	95	93	96	94	92	94	92	90	89
4	103	98	93	90	102	97	93	90	95	91	89	93	90	88	91	89	87	85
5	100	94	89	86	98	93	89	86	91	88	85	90	87	84	88	86	83	82
6	97	90	85	82	95	89	85	82	88	84	82	87	83	81	85	83	80	79
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74
9	88	81	76	73	87	80	76	73	79	76	73	79	75	73	78	75	73	72
10	85	78	74	71	84	78	74	71	77	73	71	76	73	70	76	72	70	69

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3035803
5°	2971627
10°	2708409
15°	2115796
20°	1252656
25°	465649
30°	145498
35°	64685
40°	30012
45°	14164
50°	7752
55°	4387
60°	1973
65°	1167
70°	1442
75°	0
80°	0
85°	0



TEST NUMBER: P279950

CATALOG NUMBER: LDA2B208050D010 EU2B20FL408050 2LBALD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	554.7	25.1
10°-20°	1103.0	50.0
20°-30°	451.7	20.5
30°-40°	74.8	3.4
40°-50°	17.7	0.8
50°-60°	4.7	0.2
60°-70°	1.1	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2109.4	95.5
0°-40°	2184.1	98.9
0°-60°	2206.5	99.9
0°-90°	2207.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2207.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6153	
5°	6000	555
15°	4142	1103
25°	855	452
35°	107	75
45°	20	18
55°	5	5
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P279950

CATALOG NUMBER: LDA2B208050D010 EU2B20FL408050 2LBALD1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	6153.3
1°	6132.1
2°	6103.7
3°	6078.3
4°	6044.9
5°	6000.3
6°	5934.4
7°	5848.3
8°	5725.6
9°	5576.6
10°	5406.3
11°	5208.7
12°	4985.7
13°	4731.3
14°	4448.5
15°	4142.4
17.5°	3285.0
20°	2385.9
22.5°	1527.4
25°	855.4
27.5°	451.0
30°	255.4
32.5°	162.2
35°	107.4
37.5°	70.9
40°	46.6
42.5°	30.4
45°	20.3
47.5°	14.2
50°	10.1
52.5°	7.1
55°	5.1
57.5°	3.0
60°	2.0
62.5°	1.0
65°	1.0
67.5°	1.0
70°	1.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P279950

CATALOG NUMBER: LDA2B208050D010 EU2B20FL408050 2LBALD1WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)