

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P279790

Luminaire Tested: **LDA2B159035D010 EU2B15FL409035 2LBALD1WMH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P279790
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-3)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B159035D010 EU2B15FL409035 2LBALD1WMH
Description: PORTFOLIO 2IN ADJ 1500 LUMEN LED LUMINAIRE WITH FLOOD OPTIC AND 2in
ADJ spun Refl w/lens Self-Flanged, WMH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1271.0 lumens
Efficiency: N/A
Efficacy: 90.1 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.55
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P279790

CATALOG NUMBER: LDA2B159035D010 EU2B15FL409035 2LBALD1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P279790

CATALOG NUMBER: LDA2B159035D010 EU2B15FL409035 2LBALD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	115	113	111	109	112	110	109	107	106	105	104		103	102	101		99	99	98	96
2	111	107	104	101	109	105	102	100	102	100	98		99	97	96		97	95	94	92
3	107	102	98	95	105	101	97	94	98	95	93		96	94	92		94	92	90	89
4	103	98	93	90	102	97	93	90	95	91	89		93	90	88		91	89	87	85
5	100	94	89	86	98	93	89	86	91	88	85		90	87	84		88	86	83	82
6	97	90	85	82	95	89	85	82	88	84	82		87	83	81		85	83	80	79
7	94	87	82	79	92	86	82	79	85	81	78		84	81	78		83	80	78	77
8	91	84	79	76	90	83	79	76	82	78	76		81	78	75		80	77	75	74
9	88	81	76	73	87	80	76	73	79	76	73		79	75	73		78	75	73	72
10	85	78	74	71	84	78	74	71	77	73	71		76	73	70		76	72	70	69

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1747635
5°	1710680
10°	1559177
15°	1218023
20°	721121
25°	268100
30°	83744
35°	37221
40°	17260
45°	8163
50°	4452
55°	2494
60°	1184
65°	700
70°	865
75°	0
80°	0
85°	0



TEST NUMBER: P279790

CATALOG NUMBER: LDA2B159035D010 EU2B15FL409035 2LBALD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	319.3	25.1
10°-20°	635.0	50.0
20°-30°	260.0	20.5
30°-40°	43.0	3.4
40°-50°	10.2	0.8
50°-60°	2.7	0.2
60°-70°	0.7	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1214.3	95.5
0°-40°	1257.3	98.9
0°-60°	1270.2	99.9
0°-90°	1271.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1271.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3542	
5°	3454	319
15°	2385	635
25°	492	260
35°	62	43
45°	12	10
55°	3	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P279790

CATALOG NUMBER: LDA2B159035D010 EU2B15FL409035 2LBALD1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3542.3
1°	3530.0
2°	3513.7
3°	3499.1
4°	3479.9
5°	3454.2
6°	3416.3
7°	3366.7
8°	3296.1
9°	3210.3
10°	3112.3
11°	2998.5
12°	2870.1
13°	2723.7
14°	2560.9
15°	2384.7
17.5°	1891.1
20°	1373.5
22.5°	879.3
25°	492.5
27.5°	259.6
30°	147.0
32.5°	93.4
35°	61.8
37.5°	40.8
40°	26.8
42.5°	17.5
45°	11.7
47.5°	8.2
50°	5.8
52.5°	4.1
55°	2.9
57.5°	1.8
60°	1.2
62.5°	0.6
65°	0.6
67.5°	0.6
70°	0.6
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P279790

CATALOG NUMBER: LDA2B159035D010 EU2B15FL409035 2LBALD1WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)