

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P279057

Luminaire Tested: **LDA2B208050D010 EU2B20NFL258050 2LBALD1GPH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P279057
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-2)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B208050D010 EU2B20NFL258050 2LBALD1GPH
Description: PORTFOLIO 2IN ADJ 2000 LUMEN LED LUMINAIRE WITH NARROW FLOOD OPTIC
AND 2in ADJ spun Refl w/lens Self-Flanged, GPH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2045.9 lumens
Efficiency: N/A
Efficacy: 99.3 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.39
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P279057

CATALOG NUMBER: LDA2B208050D010 EU2B20NFL258050 2LBALD1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P279057

CATALOG NUMBER: LDA2B208050D010 EU2B20NFL258050 2LBALD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|----|----|----|----|----|----|-----|----|----|---|--|--|--|--|--|--|----|--|--|--|--|--|--|--|--|---|--|--|--|--|--|--|--|--|
| RF | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | | | | | | | | | |
| RC | 80 | | | | | | | | | 70 | | | | | | | | | 50 | | | | | | | | | 30 | | | | | | | | | 10 | | | | | | | | | 0 | | | | | | | | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | | | | | | | | | | | | | | | | | | | | | | | | |
| RCR | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | | | | | | | 100 | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 1 | 115 | 113 | 111 | 110 | 113 | 111 | 109 | 108 | 107 | 106 | 105 | 103 | 102 | 102 | 100 | 99 | 99 | 97 | | | | | | | | | 97 | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 2 | 112 | 108 | 105 | 103 | 110 | 107 | 104 | 102 | 103 | 101 | 100 | 101 | 99 | 98 | 98 | 97 | 96 | 94 | | | | | | | | | 94 | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 3 | 108 | 104 | 100 | 98 | 107 | 103 | 99 | 97 | 100 | 98 | 95 | 98 | 96 | 94 | 96 | 94 | 93 | 91 | | | | | | | | | 91 | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 4 | 105 | 100 | 96 | 94 | 104 | 99 | 96 | 93 | 97 | 94 | 92 | 95 | 93 | 91 | 94 | 92 | 90 | 89 | | | | | | | | | 89 | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 5 | 102 | 97 | 93 | 90 | 101 | 96 | 92 | 90 | 94 | 91 | 89 | 93 | 90 | 88 | 92 | 89 | 87 | 86 | | | | | | | | | 86 | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 6 | 100 | 94 | 90 | 87 | 98 | 93 | 89 | 87 | 92 | 89 | 86 | 91 | 88 | 86 | 89 | 87 | 85 | 84 | | | | | | | | | 84 | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 7 | 97 | 91 | 87 | 84 | 96 | 90 | 87 | 84 | 89 | 86 | 84 | 88 | 85 | 83 | 87 | 85 | 83 | 82 | | | | | | | | | 82 | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 8 | 95 | 88 | 85 | 82 | 94 | 88 | 84 | 82 | 87 | 84 | 81 | 86 | 83 | 81 | 85 | 83 | 81 | 80 | | | | | | | | | 80 | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 9 | 92 | 86 | 82 | 80 | 92 | 86 | 82 | 80 | 85 | 82 | 79 | 84 | 81 | 79 | 84 | 81 | 79 | 78 | | | | | | | | | 78 | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 10 | 90 | 84 | 80 | 78 | 90 | 84 | 80 | 78 | 83 | 80 | 77 | 82 | 79 | 77 | 82 | 79 | 77 | 76 | | | | | | | | | 76 | | | | | | | | | | | | | | | | | | | | | | | | | | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|---------|
| | 0° |
| 0° | 5236591 |
| 5° | 4829395 |
| 10° | 3254419 |
| 15° | 1604570 |
| 20° | 685367 |
| 25° | 269460 |
| 30° | 106075 |
| 35° | 46496 |
| 40° | 22348 |
| 45° | 10745 |
| 50° | 5910 |
| 55° | 3355 |
| 60° | 1875 |
| 65° | 1167 |
| 70° | 1442 |
| 75° | 0 |
| 80° | 0 |
| 85° | 0 |



TEST NUMBER: P279057

CATALOG NUMBER: LDA2B208050D010 EU2B20NFL258050 2LBALD1GPH

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 826.0 | 40.4 |
| 10°-20° | 889.6 | 43.5 |
| 20°-30° | 256.9 | 12.6 |
| 30°-40° | 54.2 | 2.6 |
| 40°-50° | 13.3 | 0.7 |
| 50°-60° | 3.9 | 0.2 |
| 60°-70° | 1.3 | 0.1 |
| 70°-80° | 0.7 | 0.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 1972.5 | 96.4 |
| 0°-40° | 2026.7 | 99.1 |
| 0°-60° | 2043.9 | 99.9 |
| 0°-90° | 2045.9 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 2045.9 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-------|------|
| 0° | 10614 | |
| 5° | 9752 | 826 |
| 15° | 3142 | 890 |
| 25° | 495 | 257 |
| 35° | 77 | 54 |
| 45° | 15 | 13 |
| 55° | 4 | 4 |
| 65° | 1 | 1 |
| 75° | 0 | 1 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P279057

CATALOG NUMBER: LDA2B208050D010 EU2B20NFL258050 2LBALD1GPH

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|---------|
| 0° | 10614.1 |
| 1° | 10547.5 |
| 2° | 10434.6 |
| 3° | 10282.2 |
| 4° | 10066.1 |
| 5° | 9751.5 |
| 6° | 9327.0 |
| 7° | 8773.2 |
| 8° | 8092.0 |
| 9° | 7298.0 |
| 10° | 6496.2 |
| 11° | 5685.7 |
| 12° | 4920.6 |
| 13° | 4241.4 |
| 14° | 3644.2 |
| 15° | 3141.5 |
| 17.5° | 2076.3 |
| 20° | 1305.4 |
| 22.5° | 802.7 |
| 25° | 495.0 |
| 27.5° | 302.0 |
| 30° | 186.2 |
| 32.5° | 117.7 |
| 35° | 77.2 |
| 37.5° | 51.1 |
| 40° | 34.7 |
| 42.5° | 24.1 |
| 45° | 15.4 |
| 47.5° | 9.6 |
| 50° | 7.7 |
| 52.5° | 5.8 |
| 55° | 3.9 |
| 57.5° | 2.9 |
| 60° | 1.9 |
| 62.5° | 1.9 |
| 65° | 1.0 |
| 67.5° | 1.0 |
| 70° | 1.0 |
| 72.5° | 1.0 |
| 75° | 0.0 |
| 77.5° | 1.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |



TEST NUMBER: P279057

CATALOG NUMBER: LDA2B208050D010 EU2B20NFL258050 2LBALD1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







| | | |
|-------|--|-----|
| 85° | | 0.0 |
| 87.5° | | 0.0 |



(END OF REPORT)