

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P279052

Luminaire Tested: **LDA2B208050D010 EU2B20NFL258050 2LBALD1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P279052
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-2)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B208050D010 EU2B20NFL258050 2LBALD1MW
Description: PORTFOLIO 2IN ADJ 2000 LUMEN LED LUMINAIRE WITH NARROW FLOOD OPTIC
AND 2in ADJ spun Refl w/lens Self-Flanged, MW
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2045.9 lumens
Efficiency: N/A
Efficacy: 99.3 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.39
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P279052

CATALOG NUMBER: LDA2B208050D010 EU2B20NFL258050 2LBALD1MW

Luminous Intensity Polar Plot





TEST NUMBER: P279052

CATALOG NUMBER: LDA2B208050D010 EU2B20NFL258050 2LBALD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100									100																			
1	115	113	111	110	113	111	109	108	107	106	105	103	102	102	100	99	99	97									97																			
2	112	108	105	103	110	107	104	102	103	101	100	101	99	98	98	97	96	94									94																			
3	108	104	100	98	107	103	99	97	100	98	95	98	96	94	96	94	93	91									91																			
4	105	100	96	94	104	99	96	93	97	94	92	95	93	91	94	92	90	89									89																			
5	102	97	93	90	101	96	92	90	94	91	89	93	90	88	92	89	87	86									86																			
6	100	94	90	87	98	93	89	87	92	89	86	91	88	86	89	87	85	84									84																			
7	97	91	87	84	96	90	87	84	89	86	84	88	85	83	87	85	83	82									82																			
8	95	88	85	82	94	88	84	82	87	84	81	86	83	81	85	83	81	80									80																			
9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78									78																			
10	90	84	80	78	90	84	80	78	83	80	77	82	79	77	82	79	77	76									76																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	5236591
5°	4829395
10°	3254419
15°	1604570
20°	685367
25°	269460
30°	106075
35°	46496
40°	22348
45°	10745
50°	5910
55°	3355
60°	1875
65°	1167
70°	1442
75°	0
80°	0
85°	0



TEST NUMBER: P279052

CATALOG NUMBER: LDA2B208050D010 EU2B20NFL258050 2LBALD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	826.0	40.4
10°-20°	889.6	43.5
20°-30°	256.9	12.6
30°-40°	54.2	2.6
40°-50°	13.3	0.7
50°-60°	3.9	0.2
60°-70°	1.3	0.1
70°-80°	0.7	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1972.5	96.4
0°-40°	2026.7	99.1
0°-60°	2043.9	99.9
0°-90°	2045.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2045.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10614	
5°	9752	826
15°	3142	890
25°	495	257
35°	77	54
45°	15	13
55°	4	4
65°	1	1
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P279052

CATALOG NUMBER: LDA2B208050D010 EU2B20NFL258050 2LBALD1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	10614.1
1°	10547.5
2°	10434.6
3°	10282.2
4°	10066.1
5°	9751.5
6°	9327.0
7°	8773.2
8°	8092.0
9°	7298.0
10°	6496.2
11°	5685.7
12°	4920.6
13°	4241.4
14°	3644.2
15°	3141.5
17.5°	2076.3
20°	1305.4
22.5°	802.7
25°	495.0
27.5°	302.0
30°	186.2
32.5°	117.7
35°	77.2
37.5°	51.1
40°	34.7
42.5°	24.1
45°	15.4
47.5°	9.6
50°	7.7
52.5°	5.8
55°	3.9
57.5°	2.9
60°	1.9
62.5°	1.9
65°	1.0
67.5°	1.0
70°	1.0
72.5°	1.0
75°	0.0
77.5°	1.0
80°	0.0
82.5°	0.0



TEST NUMBER: P279052

CATALOG NUMBER: LDA2B208050D010 EU2B20NFL258050 2LBALD1MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)