

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P278232

Luminaire Tested: **LDA2B208050D010 EU2B20SP158050 2LBAD1WHH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P278232
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-1)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B208050D010 EU2B20SP158050 2LBAD1WHH
Description: PORTFOLIO 2IN ADJ 2000 LUMEN LED LUMINAIRE WITH SPOT OPTIC AND 2in
ADJ spun Refl, Self-Flanged, WHH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2094.1 lumens
Efficiency: N/A
Efficacy: 101.7 lumens/watt
Spacing Criteria (0/90/45): 0.28 / 0.28 / 0.28
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P278232

CATALOG NUMBER: LDA2B208050D010 EU2B20SP158050 2LBAD1WHH

Luminous Intensity Polar Plot





TEST NUMBER: P278232

CATALOG NUMBER: LDA2B208050D010 EU2B20SP158050 2LBAD1WHH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	116	114	112	110	113	112	110	109	108	106	105	104	103	102	101	100	99	98	99	98	98																
2	112	109	107	104	110	108	105	103	105	103	101	102	100	99	99	98	97	99	98	97	96																
3	109	105	102	100	108	104	101	99	102	99	98	100	98	96	97	96	95	97	96	95	93																
4	107	102	99	96	105	101	98	96	99	97	95	98	95	94	96	94	93	96	94	93	92																
5	104	99	96	93	103	99	95	93	97	94	92	96	93	91	94	92	91	94	92	91	90																
6	102	97	93	91	101	96	93	91	95	92	90	94	91	89	93	91	89	93	91	89	88																
7	100	95	91	89	99	94	91	88	93	90	88	92	90	88	91	89	87	91	89	87	86																
8	98	93	89	87	97	92	89	87	91	88	86	90	88	86	90	87	86	90	87	86	85																
9	96	91	87	85	95	90	87	85	90	87	85	89	86	84	88	86	84	88	86	84	83																
10	94	89	86	83	94	89	85	83	88	85	83	87	85	83	87	85	83	87	85	83	82																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	9460262
5°	7542305
10°	3274458
15°	1131295
20°	463859
25°	209471
30°	84256
35°	39269
40°	21318
45°	7954
50°	4759
55°	3527
60°	2072
65°	1167
70°	1442
75°	0
80°	0
85°	0



TEST NUMBER: P278232

CATALOG NUMBER: LDA2B208050D010 EU2B20SP158050 2LBAD1WHH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1151.0	55.0
10°-20°	691.2	33.0
20°-30°	190.3	9.1
30°-40°	45.3	2.2
40°-50°	11.2	0.5
50°-60°	3.7	0.2
60°-70°	1.4	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2032.5	97.1
0°-40°	2077.7	99.2
0°-60°	2092.6	99.9
0°-90°	2094.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2094.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	19175	
5°	15229	###
15°	2215	691
25°	385	190
35°	65	45
45°	11	11
55°	4	4
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P278232

CATALOG NUMBER: LDA2B208050D010 EU2B20SP158050 2LBAD1WHH

CANDELA DISTRIBUTION (FULL):

	0°
0°	19175.1
1°	18963.0
2°	18455.1
3°	17680.2
4°	16586.7
5°	15229.4
6°	13572.1
7°	11756.4
8°	9848.8
9°	8094.2
10°	6536.2
11°	5217.2
12°	4152.6
13°	3348.8
14°	2709.4
15°	2214.9
17.5°	1374.9
20°	883.5
22.5°	579.3
25°	384.8
27.5°	247.3
30°	147.9
32.5°	93.1
35°	65.2
37.5°	47.6
40°	33.1
42.5°	19.7
45°	11.4
47.5°	8.3
50°	6.2
52.5°	5.2
55°	4.1
57.5°	3.1
60°	2.1
62.5°	2.1
65°	1.0
67.5°	1.0
70°	1.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P278232

CATALOG NUMBER: LDA2B208050D010 EU2B20SP158050 2LBAD1WHH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)