

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P280681

Luminaire Tested: **LDA2B159035D010 EU2B15WFL559035 2LBAD1GPH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P280681
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-5)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B159035D010 EU2B15WFL559035 2LBAD1GPH
Description: PORTFOLIO 2IN ADJ 1500 LUMEN LED LUMINAIRE WITH WIDE FLOOD OPTIC AND
2in ADJ spun Refl, Self-Flanged, GPH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1278.9 lumens
Efficiency: N/A
Efficacy: 90.7 lumens/watt
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.73
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P280681

CATALOG NUMBER: LDA2B159035D010 EU2B15WFL559035 2LBAD1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P280681

CATALOG NUMBER: LDA2B159035D010 EU2B15WFL559035 2LBAD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	112	109	107	112	110	108	106	106	104	103	102	101	99	98	97	97	95																			
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	90																			
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	88	86	85																			
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	80																			
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76																			
6	92	84	79	75	91	84	79	75	82	78	75	81	77	74	80	76	74	72																			
7	88	80	75	71	87	80	75	71	78	74	71	77	73	70	76	73	70	69																			
8	85	76	71	68	84	76	71	67	75	70	67	74	70	67	73	69	67	65																			
9	81	73	68	64	80	72	68	64	72	67	64	71	67	64	70	66	64	62																			
10	78	70	65	61	77	69	64	61	69	64	61	68	64	61	67	63	61	59																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1092155
5°	1069930
10°	994932
15°	868710
20°	719231
25°	550080
30°	301022
35°	111422
40°	38578
45°	17373
50°	8213
55°	4043
60°	1184
65°	700
70°	865
75°	0
80°	0
85°	0



TEST NUMBER: P280681

CATALOG NUMBER: LDA2B159035D010 EU2B15WFL559035 2LBAD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	200.7	15.7
10°-20°	470.1	36.8
20°-30°	444.3	34.7
30°-40°	136.8	10.7
40°-50°	21.6	1.7
50°-60°	4.6	0.4
60°-70°	0.7	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1115.1	87.2
0°-40°	1251.9	97.9
0°-60°	1278.1	99.9
0°-90°	1278.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1278.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2214	
5°	2160	201
15°	1701	470
25°	1010	444
35°	185	137
45°	25	22
55°	5	5
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P280681

CATALOG NUMBER: LDA2B159035D010 EU2B15WFL559035 2LBAD1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2213.7
1°	2205.4
2°	2195.4
3°	2187.1
4°	2176.4
5°	2160.4
6°	2139.6
7°	2111.7
8°	2074.4
9°	2031.1
10°	1986.0
11°	1936.2
12°	1883.4
13°	1825.9
14°	1766.0
15°	1700.8
17.5°	1528.2
20°	1369.9
22.5°	1209.2
25°	1010.5
27.5°	770.9
30°	528.4
32.5°	324.4
35°	185.0
37.5°	103.2
40°	59.9
42.5°	37.4
45°	24.9
47.5°	16.6
50°	10.7
52.5°	7.1
55°	4.7
57.5°	3.0
60°	1.2
62.5°	0.6
65°	0.6
67.5°	0.6
70°	0.6
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P280681

CATALOG NUMBER: LDA2B159035D010 EU2B15WFL559035 2LBAD1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)