

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P280845

Luminaire Tested: **LDA2B208050D010 EU2B20WFL558050 2LBALD1B**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P280845
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-5)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B208050D010 EU2B20WFL558050 2LBALD1B
Description: PORTFOLIO 2IN ADJ 2000 LUMEN LED LUMINAIRE WITH WIDE FLOOD OPTIC AND
2in ADJ spun Refl w/lens Self-Flanged, B
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2191.8 lumens
Efficiency: N/A
Efficacy: 106.4 lumens/watt
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.73
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P280845

CATALOG NUMBER: LDA2B208050D010 EU2B20WFL558050 2LBALD1B

Luminous Intensity Polar Plot





TEST NUMBER: P280845

CATALOG NUMBER: LDA2B208050D010 EU2B20WFL558050 2LBALD1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	112	109	107	112	110	108	106	106	104	103	102	101	99	98	97	97	95			95
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	90			90
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	88	86	85			85
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	80			80
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76			76
6	92	84	79	75	91	84	79	75	82	78	75	81	77	74	80	76	74	72			72
7	88	80	75	71	87	80	75	71	78	74	71	77	73	70	76	73	70	69			69
8	85	76	71	68	84	76	71	67	75	70	67	74	70	67	73	69	67	65			65
9	81	73	68	64	80	72	68	64	72	67	64	71	67	64	70	66	64	62			62
10	78	70	65	61	77	69	64	61	69	64	61	68	64	61	67	63	61	59			59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1871913
5°	1833798
10°	1705261
15°	1488882
20°	1232705
25°	942839
30°	515907
35°	190984
40°	66143
45°	29793
50°	14046
55°	6967
60°	1973
65°	1167
70°	1442
75°	0
80°	0
85°	0



TEST NUMBER: P280845

CATALOG NUMBER: LDA2B208050D010 EU2B20WFL558050 2LBALD1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	344.1	15.7
10°-20°	805.7	36.8
20°-30°	761.5	34.7
30°-40°	234.4	10.7
40°-50°	37.1	1.7
50°-60°	7.8	0.4
60°-70°	1.1	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1911.3	87.2
0°-40°	2145.7	97.9
0°-60°	2190.6	99.9
0°-90°	2191.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2191.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3794	
5°	3703	344
15°	2915	806
25°	1732	762
35°	317	234
45°	43	37
55°	8	8
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P280845

CATALOG NUMBER: LDA2B208050D010 EU2B20WFL558050 2LBALD1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	3794.2
1°	3780.0
2°	3762.7
3°	3748.5
4°	3730.2
5°	3702.8
6°	3667.2
7°	3619.4
8°	3555.4
9°	3481.2
10°	3403.9
11°	3318.6
12°	3228.1
13°	3129.5
14°	3026.9
15°	2915.0
17.5°	2619.3
20°	2347.9
22.5°	2072.4
25°	1732.0
27.5°	1321.3
30°	905.6
32.5°	556.0
35°	317.1
37.5°	176.9
40°	102.7
42.5°	64.0
45°	42.7
47.5°	28.5
50°	18.3
52.5°	12.2
55°	8.1
57.5°	5.1
60°	2.0
62.5°	1.0
65°	1.0
67.5°	1.0
70°	1.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P280845

CATALOG NUMBER: LDA2B208050D010 EU2B20WFL558050 2LBALD1B

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)