

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P280682

Luminaire Tested: **LDA2B159035D010 EU2B15WFL559035 2LBALD1LI**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P280682  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-5)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA2B159035D010 EU2B15WFL559035 2LBALD1LI  
Description: PORTFOLIO 2IN ADJ 1500 LUMEN LED LUMINAIRE WITH WIDE FLOOD OPTIC AND  
2in ADJ spun Refl w/lens Self-Flanged, H  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1267.0 lumens  
Efficiency: N/A  
Efficacy: 89.9 lumens/watt  
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.73  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P280682

CATALOG NUMBER: LDA2B159035D010 EU2B15WFL559035 2LBALD1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P280682

CATALOG NUMBER: LDA2B159035D010 EU2B15WFL559035 2LBALD1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	112	109	107	112	110	108	106	106	104	103	102	101	99	98	97	97	95			
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	90			
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	88	86	85			
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	80			
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76			
6	92	84	79	75	91	84	79	75	82	78	75	81	77	74	80	76	74	72			
7	88	80	75	71	87	80	75	71	78	74	71	77	73	70	76	73	70	69			
8	85	76	71	68	84	76	71	67	75	70	67	74	70	67	73	69	67	65			
9	81	73	68	64	80	72	68	64	72	67	64	71	67	64	70	66	64	62			
10	78	70	65	61	77	69	64	61	69	64	61	68	64	61	67	63	61	59			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1082041
5°	1059976
10°	985714
15°	860640
20°	712563
25°	544963
30°	298230
35°	110399
40°	38191
45°	17234
50°	8136
55°	4043
60°	1184
65°	700
70°	865
75°	0
80°	0
85°	0



TEST NUMBER: P280682

CATALOG NUMBER: LDA2B159035D010 EU2B15WFL559035 2LBALD1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	198.9	15.7
10°-20°	465.7	36.8
20°-30°	440.2	34.7
30°-40°	135.5	10.7
40°-50°	21.4	1.7
50°-60°	4.5	0.4
60°-70°	0.7	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1104.8	87.2
0°-40°	1240.3	97.9
0°-60°	1266.2	99.9
0°-90°	1267.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1267.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2193	
5°	2140	199
15°	1685	466
25°	1001	440
35°	183	136
45°	25	21
55°	5	5
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P280682

CATALOG NUMBER: LDA2B159035D010 EU2B15WFL559035 2LBALD1LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2193.2
1°	2185.0
2°	2175.0
3°	2166.8
4°	2156.2
5°	2140.3
6°	2119.7
7°	2092.1
8°	2055.1
9°	2012.2
10°	1967.6
11°	1918.2
12°	1865.9
13°	1809.0
14°	1749.6
15°	1685.0
17.5°	1514.0
20°	1357.2
22.5°	1197.9
25°	1001.1
27.5°	763.8
30°	523.5
32.5°	321.4
35°	183.3
37.5°	102.2
40°	59.3
42.5°	37.0
45°	24.7
47.5°	16.5
50°	10.6
52.5°	7.1
55°	4.7
57.5°	2.9
60°	1.2
62.5°	0.6
65°	0.6
67.5°	0.6
70°	0.6
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P280682

CATALOG NUMBER: LDA2B159035D010 EU2B15WFL559035 2LBALD1LI

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)