

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P279060

Luminaire Tested: **LDA2B209024D010 EU2B20NFL259024 2LBAD1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P279060
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-2)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B209024D010 EU2B20NFL259024 2LBAD1MW
Description: PORTFOLIO 2IN ADJ 2000 LUMEN LED LUMINAIRE WITH NARROW FLOOD OPTIC AND 2in ADJ spun Refl, Self-Flanged, MW
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1505.2 lumens
Efficiency: N/A
Efficacy: 73.1 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.39
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P279060

CATALOG NUMBER: LDA2B209024D010 EU2B20NFL259024 2LBAD1MW

Luminous Intensity Polar Plot





TEST NUMBER: P279060

CATALOG NUMBER: LDA2B209024D010 EU2B20NFL259024 2LBAD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100									100																											
1	115	113	111	110	113	111	109	108	107	106	105	103	102	102	100	99	99	97									97																											
2	112	108	105	103	110	107	104	102	103	101	100	101	99	98	98	97	96	94									94																											
3	108	104	100	98	107	103	99	97	100	98	95	98	96	94	96	94	93	91									91																											
4	105	100	96	94	104	99	96	93	97	94	92	95	93	91	94	92	90	89									89																											
5	102	97	93	90	101	96	92	90	94	91	89	93	90	88	92	89	87	86									86																											
6	100	94	90	87	98	93	89	87	92	89	86	91	88	86	89	87	85	84									84																											
7	97	91	87	84	96	90	87	84	89	86	84	88	85	83	87	85	83	82									82																											
8	95	88	85	82	94	88	84	82	87	84	81	86	83	81	85	83	81	80									80																											
9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78									78																											
10	90	84	80	78	90	84	80	78	83	80	77	82	79	77	82	79	77	76									76																											

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3852662
5°	3553095
10°	2394349
15°	1180533
20°	504234
25°	198258
30°	78047
35°	34210
40°	16487
45°	7954
50°	4375
55°	2408
60°	1381
65°	817
70°	1010
75°	0
80°	0
85°	0



TEST NUMBER: P279060

CATALOG NUMBER: LDA2B209024D010 EU2B20NFL259024 2LBAD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	607.7	40.4
10°-20°	654.5	43.5
20°-30°	189.0	12.6
30°-40°	39.9	2.7
40°-50°	9.8	0.7
50°-60°	2.8	0.2
60°-70°	0.9	0.1
70°-80°	0.5	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1451.2	96.4
0°-40°	1491.1	99.1
0°-60°	1503.8	99.9
0°-90°	1505.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1505.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7809	
5°	7174	608
15°	2311	655
25°	364	189
35°	57	40
45°	11	10
55°	3	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P279060

CATALOG NUMBER: LDA2B209024D010 EU2B20NFL259024 2LBAD1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	7809.0
1°	7760.0
2°	7677.0
3°	7564.8
4°	7405.8
5°	7174.4
6°	6862.1
7°	6454.6
8°	5953.5
9°	5369.3
10°	4779.4
11°	4183.1
12°	3620.2
13°	3120.5
14°	2681.1
15°	2311.3
17.5°	1527.6
20°	960.4
22.5°	590.6
25°	364.2
27.5°	222.2
30°	137.0
32.5°	86.6
35°	56.8
37.5°	37.6
40°	25.6
42.5°	17.7
45°	11.4
47.5°	7.1
50°	5.7
52.5°	4.3
55°	2.8
57.5°	2.1
60°	1.4
62.5°	1.4
65°	0.7
67.5°	0.7
70°	0.7
72.5°	0.7
75°	0.0
77.5°	0.7
80°	0.0
82.5°	0.0



TEST NUMBER: P279060

CATALOG NUMBER: LDA2B209024D010 EU2B20NFL259024 2LBAD1MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)