

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P278236

Luminaire Tested: **LDA2B209024D010 EU2B20SP159024 2LBAD1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P278236
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-1)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B209024D010 EU2B20SP159024 2LBAD1MW
Description: PORTFOLIO 2IN ADJ 2000 LUMEN LED LUMINAIRE WITH SPOT OPTIC AND 2in
ADJ spun Refl, Self-Flanged, MW
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1437.0 lumens
Efficiency: N/A
Efficacy: 69.8 lumens/watt
Spacing Criteria (0/90/45): 0.28 / 0.28 / 0.28
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P278236

CATALOG NUMBER: LDA2B209024D010 EU2B20SP159024 2LBAD1MW

Luminous Intensity Polar Plot





TEST NUMBER: P278236

CATALOG NUMBER: LDA2B209024D010 EU2B20SP159024 2LBAD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	116	114	112	110	113	112	110	109	108	106	105	104	103	102	101	100	99	98	99		98
2	112	109	107	104	110	108	105	103	105	103	101	102	100	99	99	98	97	96	99		96
3	109	105	102	100	108	104	101	99	102	99	98	100	98	96	97	96	95	93	97		93
4	107	102	99	96	105	101	98	96	99	97	95	98	95	94	96	94	93	92	96		92
5	104	99	96	93	103	99	95	93	97	94	92	96	93	91	94	92	91	90	94		90
6	102	97	93	91	101	96	93	91	95	92	90	94	91	89	93	91	89	88	93		88
7	100	95	91	89	99	94	91	88	93	90	88	92	90	88	91	89	87	86	91		86
8	98	93	89	87	97	92	89	87	91	88	86	90	88	86	90	87	86	85	90		85
9	96	91	87	85	95	90	87	85	90	87	85	89	86	84	88	86	84	83	88		83
10	94	89	86	83	94	89	85	83	88	85	83	87	85	83	87	85	83	82	87		82

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	6492049
5°	5175869
10°	2247063
15°	776364
20°	318322
25°	143767
30°	57823
35°	26922
40°	14620
45°	5442
50°	3300
55°	2408
60°	1381
65°	817
70°	1010
75°	0
80°	0
85°	0



TEST NUMBER: P278236

CATALOG NUMBER: LDA2B209024D010 EU2B20SP159024 2LBAD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	789.8	55.0
10°-20°	474.3	33.0
20°-30°	130.6	9.1
30°-40°	31.1	2.2
40°-50°	7.7	0.5
50°-60°	2.5	0.2
60°-70°	0.9	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1394.8	97.1
0°-40°	1425.8	99.2
0°-60°	1436.0	99.9
0°-90°	1437.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1437.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	13159	
5°	10451	790
15°	1520	474
25°	264	131
35°	45	31
45°	8	8
55°	3	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P278236

CATALOG NUMBER: LDA2B209024D010 EU2B20SP159024 2LBAD1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	13158.8
1°	13013.3
2°	12664.7
3°	12132.9
4°	11382.5
5°	10451.1
6°	9313.8
7°	8067.8
8°	6758.7
9°	5554.6
10°	4485.4
11°	3580.2
12°	2849.7
13°	2298.1
14°	1859.3
15°	1520.0
17.5°	943.5
20°	606.3
22.5°	397.6
25°	264.1
27.5°	169.7
30°	101.5
32.5°	63.9
35°	44.7
37.5°	32.7
40°	22.7
42.5°	13.5
45°	7.8
47.5°	5.7
50°	4.3
52.5°	3.5
55°	2.8
57.5°	2.1
60°	1.4
62.5°	1.4
65°	0.7
67.5°	0.7
70°	0.7
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P278236

CATALOG NUMBER: LDA2B209024D010 EU2B20SP159024 2LBAD1MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)