

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P315155

Luminaire Tested: **LDA2B20NFL9024D010 PIN1MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P315155
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-2)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B20NFL9024D010 PIN1MMS
Description: PORTFOLIO 2IN ADJ 2000 LUMEN LED LUMINAIRE WITH NARROW FLOOD OPTIC
AND 2in Adj PinHole, Black oculus, matte metallic silver finish
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1303.7 lumens
Efficiency: N/A
Efficacy: 63.3 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.39
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P315155

CATALOG NUMBER: LDA2B20NFL9024D010 PIN1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P315155

CATALOG NUMBER: LDA2B20NFL9024D010 PIN1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100	100	100	100	100	100	100	100	100													
	1	115	113	111	110	113	111	109	108	107	106	105	103	102	102	100	99	99	97	97	97	97	97	97	97	97	97	97	97	97	97	97													
	2	112	108	105	103	110	107	104	102	103	101	100	101	99	98	98	97	96	94	94	94	94	94	94	94	94	94	94	94	94	94	94													
	3	108	104	100	98	107	103	99	97	100	98	95	98	96	94	96	94	93	91	91	91	91	91	91	91	91	91	91	91	91	91	91	91												
	4	105	100	96	94	104	99	96	93	97	94	92	95	93	91	94	92	90	89	89	89	89	89	89	89	89	89	89	89	89	89	89	89												
	5	102	97	93	90	101	96	92	90	94	91	89	93	90	88	92	89	87	86	86	86	86	86	86	86	86	86	86	86	86	86	86	86												
	6	100	94	90	87	98	93	89	87	92	89	86	91	88	86	89	87	85	84	84	84	84	84	84	84	84	84	84	84	84	84	84	84	84											
	7	97	91	87	84	96	90	87	84	89	86	84	88	85	83	87	85	83	82	82	82	82	82	82	82	82	82	82	82	82	82	82	82	82											
	8	95	88	85	82	94	88	84	82	87	84	81	86	83	81	85	83	81	80	80	80	80	80	80	80	80	80	80	80	80	80	80	80	80											
	9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78	78	78	78	78	78	78	78	78	78	78	78	78	78	78	78											
	10	90	84	80	78	90	84	80	78	83	80	78	82	79	77	82	79	77	76	76	76	76	76	76	76	76	76	76	76	76	76	76	76	76											

AVERAGE LUMINANCE (cd/sqm):

	0°	
0°	3337099	
5°	3077609	
10°	2073927	
15°	1022553	
20°	436768	
25°	171693	
30°	67622	
35°	29632	
40°	14233	
45°	6838	
50°	3761	
55°	2150	
60°	1184	
65°	700	
70°	865	
75°	0	
80°	0	
85°	0	



TEST NUMBER: P315155

CATALOG NUMBER: LDA2B20NFL9024D010 PIN1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	526.4	40.4
10°-20°	566.9	43.5
20°-30°	163.7	12.6
30°-40°	34.6	2.7
40°-50°	8.5	0.7
50°-60°	2.4	0.2
60°-70°	0.8	0.1
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1257.0	96.4
0°-40°	1291.6	99.1
0°-60°	1302.5	99.9
0°-90°	1303.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1303.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6764	
5°	6214	526
15°	2002	567
25°	315	164
35°	49	35
45°	10	8
55°	2	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P315155

CATALOG NUMBER: LDA2B20NFL9024D010 PIN1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	6764.0
1°	6721.5
2°	6649.6
3°	6552.5
4°	6414.7
5°	6214.3
6°	5943.8
7°	5590.8
8°	5156.7
9°	4650.7
10°	4139.8
11°	3623.3
12°	3135.7
13°	2702.9
14°	2322.3
15°	2002.0
17.5°	1323.2
20°	831.9
22.5°	511.6
25°	315.4
27.5°	192.4
30°	118.7
32.5°	75.0
35°	49.2
37.5°	32.6
40°	22.1
42.5°	15.4
45°	9.8
47.5°	6.1
50°	4.9
52.5°	3.7
55°	2.5
57.5°	1.8
60°	1.2
62.5°	1.2
65°	0.6
67.5°	0.6
70°	0.6
72.5°	0.6
75°	0.0
77.5°	0.6
80°	0.0
82.5°	0.0



TEST NUMBER: P315155

CATALOG NUMBER: LDA2B20NFL9024D010 PIN1MMS

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)