

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P499504

Luminaire Tested: **LDA2B159050R60D010 2LBDLC1MB**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P499504  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-55)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B159050R60D010 2LBDLC1MB  
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 5000K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1218.9 lumens  
Efficiency: N/A  
Efficacy: 86.4 lumens/watt  
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.86  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 14.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P499504

CATALOG NUMBER: LDA2B159050R60D010 2LBDLC1MB

### Luminous Intensity Polar Plot





TEST NUMBER: P499504

CATALOG NUMBER: LDA2B159050R60D010 2LBDLC1MB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	101		101	100	98		98	97	96	94
2	108	103	100	96	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	95	91	87	93	89	86		90	87	85		88	85	83	82
4	98	90	85	81	96	89	84	81	87	83	80		85	82	79		83	80	78	76
5	93	85	79	75	91	84	79	75	82	78	74		81	77	73		79	76	73	71
6	89	80	74	70	87	79	74	70	78	73	69		76	72	69		75	71	68	67
7	84	75	69	65	83	74	69	65	73	68	65		72	68	64		71	67	64	63
8	80	71	65	61	79	70	65	61	69	64	61		68	64	60		67	63	60	59
9	76	67	61	57	75	67	61	57	66	61	57		65	60	57		64	60	57	55
10	73	63	58	54	72	63	58	54	62	57	54		61	57	54		61	57	54	52

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	721394
5°	702606
10°	683227
15°	649388
20°	593330
25°	509525
30°	379125
35°	222604
40°	106073
45°	49538
50°	24638
55°	8602
60°	1973
65°	1518
70°	1010
75°	1334
80°	0
85°	0



TEST NUMBER: P499504

CATALOG NUMBER: LDA2B159050R60D010 2LBDLC1MB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	133.5	11.0
10°-20°	353.8	29.0
20°-30°	420.0	34.5
30°-40°	237.1	19.5
40°-50°	61.7	5.1
50°-60°	11.2	0.9
60°-70°	1.1	0.1
70°-80°	0.5	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	907.3	74.4
0°-40°	1144.4	93.9
0°-60°	1217.3	99.9
0°-90°	1218.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1218.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1462	
5°	1419	133
15°	1271	354
25°	936	420
35°	370	237
45°	71	62
55°	10	11
65°	1	1
75°	1	0
85°	0	0
90°	0	



TEST NUMBER: P499504

CATALOG NUMBER: LDA2B159050R60D010 2LBDLC1MB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1462.2
1°	1462.9
2°	1452.8
3°	1444.1
4°	1427.4
5°	1418.7
6°	1403.3
7°	1391.9
8°	1381.2
9°	1373.8
10°	1363.8
11°	1344.4
12°	1326.3
13°	1316.3
14°	1292.8
15°	1271.4
16°	1246.6
17°	1217.2
18°	1189.1
19°	1155.6
20°	1130.1
21°	1095.3
22.5°	1037.7
23°	1027.7
24°	978.8
25°	936.0
26°	888.4
27°	833.5
28°	779.3
29°	726.4
30°	665.5
32.5°	512.2
35°	369.6
37.5°	252.4
40°	164.7
42.5°	107.8
45°	71.0
47.5°	48.2
50°	32.1
52.5°	20.1
55°	10.0
57.5°	4.0
60°	2.0
62.5°	1.3
65°	1.3



TEST NUMBER: P499504

CATALOG NUMBER: LDA2B159050R60D010 2LBDLC1MB

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.7
70°	0.7
72.5°	0.7
75°	0.7
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)