

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P280027

Luminaire Tested: **LDA2B209040D010 EU2B20FL409040 2LBALD1H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P280027
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-3)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B209040D010 EU2B20FL409040 2LBALD1H
Description: PORTFOLIO 2IN ADJ 2000 LUMEN LED LUMINAIRE WITH FLOOD OPTIC AND 2in
ADJ spun Refl w/lens Self-Flanged, LI
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1846.5 lumens
Efficiency: N/A
Efficacy: 89.6 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.55
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P280027

CATALOG NUMBER: LDA2B209040D010 EU2B20FL409040 2LBALD1H

Luminous Intensity Polar Plot





TEST NUMBER: P280027

CATALOG NUMBER: LDA2B209040D010 EU2B20FL409040 2LBALD1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																																				
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																																				
3	107	102	98	95	105	101	97	94	98	95	93	96	94	92	94	92	90	89																																				
4	103	98	93	90	102	97	93	90	95	91	89	93	90	88	91	89	87	85																																				
5	100	94	89	86	98	93	89	86	91	88	85	90	87	84	88	86	84	82																																				
6	97	90	85	82	95	89	85	82	88	84	82	87	83	81	85	83	80	79																																				
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																																				
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																																				
9	88	81	76	73	87	80	76	73	79	76	73	79	75	73	78	75	73	72																																				
10	85	78	74	71	84	78	74	71	77	73	71	76	73	70	76	72	70	69																																				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2539136
5°	2485443
10°	2265298
15°	1769650
20°	1047739
25°	389493
30°	121685
35°	54145
40°	25117
45°	11861
50°	6524
55°	3613
60°	1677
65°	934
70°	1154
75°	0
80°	0
85°	0



TEST NUMBER: P280027

CATALOG NUMBER: LDA2B209040D010 EU2B20FL409040 2LBALD1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	463.9	25.1
10°-20°	922.5	50.0
20°-30°	377.8	20.5
30°-40°	62.5	3.4
40°-50°	14.8	0.8
50°-60°	3.9	0.2
60°-70°	0.9	0.0
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1764.3	95.5
0°-40°	1826.8	98.9
0°-60°	1845.5	99.9
0°-90°	1846.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1846.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5147	
5°	5019	464
15°	3465	923
25°	716	378
35°	90	63
45°	17	15
55°	4	4
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P280027

CATALOG NUMBER: LDA2B209040D010 EU2B20FL409040 2LBALD1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	5146.6
1°	5128.8
2°	5105.0
3°	5083.8
4°	5055.9
5°	5018.6
6°	4963.5
7°	4891.4
8°	4788.8
9°	4664.2
10°	4521.8
11°	4356.5
12°	4170.0
13°	3957.2
14°	3720.7
15°	3464.7
17.5°	2747.5
20°	1995.6
22.5°	1277.5
25°	715.5
27.5°	377.2
30°	213.6
32.5°	135.6
35°	89.9
37.5°	59.3
40°	39.0
42.5°	25.4
45°	17.0
47.5°	11.9
50°	8.5
52.5°	5.9
55°	4.2
57.5°	2.5
60°	1.7
62.5°	0.8
65°	0.8
67.5°	0.8
70°	0.8
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P280027

CATALOG NUMBER: LDA2B209040D010 EU2B20FL409040 2LBALD1H

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)