

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P315762

Luminaire Tested: **LDA2B15WFL9035D010 PINW1MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P315762
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1809-951-61)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B15WFL9035D010 PINW1MMS
Description: PORTFOLIO 2IN ADJ 1500 LUMEN LED LUMINAIRE WITH WIDE FLOOD OPTIC AND
2in Adj PinHole, White oculus, matte metallic silver finish
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1040.6 lumens
Efficiency: N/A
Efficacy: 73.8 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.68
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P315762

CATALOG NUMBER: LDA2B15WFL9035D010 PINW1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P315762

CATALOG NUMBER: LDA2B15WFL9035D010 PINW1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94																			
2	109	104	101	98	107	103	99	96	100	97	94	97	94	92	94	92	90	89																			
3	104	98	94	90	102	97	93	89	94	91	88	92	89	87	90	87	85	84																			
4	100	93	88	84	98	92	87	83	90	86	82	88	84	81	86	83	81	79																			
5	95	88	82	79	94	87	82	78	85	81	78	84	80	77	82	79	76	75																			
6	91	83	78	74	90	82	77	74	81	77	73	80	76	73	78	75	72	71																			
7	87	79	74	70	86	78	73	70	77	73	69	76	72	69	75	71	69	67																			
8	84	75	70	66	83	75	70	66	74	69	66	73	69	66	72	68	65	64																			
9	81	72	67	63	80	71	66	63	71	66	63	70	66	63	69	65	62	61																			
10	77	69	64	60	76	68	63	60	68	63	60	67	63	60	66	62	60	58																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	946515	946515	946515
5°	918088	920316	916156
10°	840382	837025	831965
15°	706849	713438	705725
20°	540565	554899	539673
25°	343276	386989	349972
30°	199618	225367	203150
35°	105520	112266	105881
40°	55709	58221	55709
45°	31118	32304	31537
50°	14583	18421	14583
55°	5247	10064	5763
60°	6019	6019	6019
65°	6537	7121	6537
70°	8078	7212	8078
75°	7434	7434	7434
80°	7955	6251	7955
85°	6227	6227	6227



TEST NUMBER: P315762

CATALOG NUMBER: LDA2B15WFL9035D010 PINW1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	171.3	16.5
10°-20°	381.3	36.6
20°-30°	307.9	29.6
30°-40°	121.7	11.7
40°-50°	37.4	3.6
50°-60°	9.6	0.9
60°-70°	5.8	0.6
70°-80°	4.3	0.4
80°-90°	1.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	860.5	82.7
0°-40°	982.2	94.4
0°-60°	1029.2	98.9
0°-90°	1040.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1040.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1918	1918	1918	1918	1918	
5°	1854	1857	1858	1854	1850	172
15°	1384	1388	1397	1391	1382	380
25°	631	661	711	673	643	294
35°	175	180	186	181	176	117
45°	45	45	46	46	45	36
55°	6	8	12	8	7	8
65°	6	6	6	6	6	6
75°	4	4	4	4	4	4
85°	1	1	1	1	1	1
90°	0	0	0	0	0	



TEST NUMBER: P315762

CATALOG NUMBER: LDA2B15WFL9035D010 PINW1MMS

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1918.5	1918.5	1918.5	1918.5	1918.5
2.5°	1894.5	1895.7	1897.3	1895.1	1889.5
5°	1853.8	1857.2	1858.3	1854.4	1849.9
7.5°	1786.8	1782.9	1786.3	1779.6	1774.0
10°	1677.5	1672.4	1670.8	1660.7	1660.7
12.5°	1542.4	1540.7	1541.9	1536.8	1529.0
15°	1383.9	1387.8	1396.8	1391.2	1381.7
17.5°	1216.0	1221.5	1229.4	1227.7	1214.9
20°	1029.6	1045.8	1056.9	1046.3	1027.9
22.5°	817.5	852.1	880.6	858.3	828.1
25°	630.6	660.7	710.9	673.0	642.9
27.5°	478.2	500.0	545.8	508.4	487.7
30°	350.4	363.8	395.6	371.1	356.6
32.5°	250.6	260.0	273.4	258.9	251.7
35°	175.2	180.2	186.4	180.8	175.8
37.5°	123.3	125.0	129.5	125.0	122.8
40°	86.5	87.1	90.4	87.6	86.5
42.5°	62.5	62.5	64.2	63.1	62.5
45°	44.6	45.2	46.3	45.8	45.2
47.5°	31.8	32.9	32.9	33.5	31.3
50°	19.0	23.4	24.0	23.4	19.0
52.5°	10.0	14.0	17.3	14.0	10.0
55°	6.1	8.4	11.7	8.4	6.7
57.5°	6.1	6.1	7.8	6.7	6.1
60°	6.1	6.1	6.1	6.1	6.1
62.5°	6.1	6.1	6.1	6.1	6.1
65°	5.6	6.1	6.1	6.1	5.6
67.5°	5.6	5.6	5.6	5.6	5.6
70°	5.6	5.6	5.0	5.6	5.6
72.5°	5.0	5.0	4.5	5.0	5.0
75°	3.9	3.9	3.9	3.9	3.9
77.5°	3.3	3.3	3.3	3.3	3.3
80°	2.8	2.8	2.2	2.8	2.8
82.5°	1.7	1.7	1.7	1.7	1.7
85°	1.1	1.1	1.1	1.1	1.1
87.5°	0.6	0.6	0.6	0.6	0.6
90°	0.0	0.0	0.0	0.0	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180° - - 45°-225° - - - - 90°-270°







(END OF REPORT)