

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P279136

Luminaire Tested: **LDA2B209040D010 EU2B20NFL259040 2LBALD1WHH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P279136
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-2)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B209040D010 EU2B20NFL259040 2LBALD1WHH
Description: PORTFOLIO 2IN ADJ 2000 LUMEN LED LUMINAIRE WITH NARROW FLOOD OPTIC
AND 2in ADJ spun Refl w/lens Self-Flanged, WHH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1673.3 lumens
Efficiency: N/A
Efficacy: 81.2 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.39
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P279136

CATALOG NUMBER: LDA2B209040D010 EU2B20NFL259040 2LBALD1WHH

Luminous Intensity Polar Plot





TEST NUMBER: P279136

CATALOG NUMBER: LDA2B209040D010 EU2B20NFL259040 2LBALD1WHH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100	100													
1	115	113	111	110	113	111	109	108	107	106	105	103	102	102	100	99	99	97	97	97	97	97	97	97													
2	112	108	105	103	110	107	104	102	103	101	100	101	99	98	98	97	96	94	94	94	94	94	94	94													
3	108	104	100	98	107	103	99	97	100	98	95	98	96	94	96	94	93	91	91	91	91	91	91	91													
4	105	100	96	94	104	99	96	93	97	94	92	95	93	91	94	92	90	89	89	89	89	89	89	89													
5	102	97	93	90	101	96	92	90	94	91	89	93	90	88	92	89	87	86	86	86	86	86	86	86													
6	100	94	90	87	98	93	89	87	92	89	86	91	88	86	89	87	85	84	84	84	84	84	84	84													
7	97	91	87	84	96	90	87	84	89	86	84	88	85	83	87	85	83	82	82	82	82	82	82	82													
8	95	88	85	82	94	88	84	82	87	84	81	86	83	81	85	83	81	80	80	80	80	80	80	80													
9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78	78	78	78	78	78	78													
10	90	84	80	78	90	84	80	78	83	80	77	82	79	77	82	79	77	76	76	76	76	76	76	76													

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4283022
5°	3949986
10°	2661818
15°	1312361
20°	560569
25°	220359
30°	86763
35°	38004
40°	18291
45°	8791
50°	4835
55°	2752
60°	1579
65°	934
70°	1154
75°	0
80°	0
85°	0



TEST NUMBER: P279136

CATALOG NUMBER: LDA2B209040D010 EU2B20NFL259040 2LBALD1WHH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	675.6	40.4
10°-20°	727.6	43.5
20°-30°	210.1	12.6
30°-40°	44.3	2.6
40°-50°	10.9	0.7
50°-60°	3.2	0.2
60°-70°	1.1	0.1
70°-80°	0.5	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1613.3	96.4
0°-40°	1657.7	99.1
0°-60°	1671.7	99.9
0°-90°	1673.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1673.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8681	
5°	7976	676
15°	2569	728
25°	405	210
35°	63	44
45°	13	11
55°	3	3
65°	1	1
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P279136

CATALOG NUMBER: LDA2B209040D010 EU2B20NFL259040 2LBALD1WHH

CANDELA DISTRIBUTION (FULL):

	0°
0°	8681.3
1°	8626.9
2°	8534.6
3°	8409.9
4°	8233.1
5°	7975.8
6°	7628.6
7°	7175.7
8°	6618.5
9°	5969.1
10°	5313.3
11°	4650.4
12°	4024.6
13°	3469.1
14°	2980.6
15°	2569.4
17.5°	1698.2
20°	1067.7
22.5°	656.6
25°	404.8
27.5°	247.0
30°	152.3
32.5°	96.3
35°	63.1
37.5°	41.8
40°	28.4
42.5°	19.7
45°	12.6
47.5°	7.9
50°	6.3
52.5°	4.7
55°	3.2
57.5°	2.4
60°	1.6
62.5°	1.6
65°	0.8
67.5°	0.8
70°	0.8
72.5°	0.8
75°	0.0
77.5°	0.8
80°	0.0
82.5°	0.0



TEST NUMBER: P279136

CATALOG NUMBER: LDA2B209040D010 EU2B20NFL259040 2LBALD1WHH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)