

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P280927

Luminaire Tested: **LDA2B209040D010 EU2B20WFL559040 2LBALD1WH**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P280927  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-5)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA2B209040D010 EU2B20WFL559040 2LBALD1WH  
Description: PORTFOLIO 2IN ADJ 2000 LUMEN LED LUMINAIRE WITH WIDE FLOOD OPTIC AND  
2in ADJ spun Refl w/lens Self-Flanged, WH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1812.9 lumens  
Efficiency: N/A  
Efficacy: 88.0 lumens/watt  
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.73  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 20.6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P280927

CATALOG NUMBER: LDA2B209040D010 EU2B20WFL559040 2LBALD1WH

### Luminous Intensity Polar Plot





TEST NUMBER: P280927

CATALOG NUMBER: LDA2B209040D010 EU2B20WFL559040 2LBALD1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20																		
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	114	112	109	107	112	110	108	106	106	104	103	102	101	99	98	97	97	95	95	93	91	88	86	85	85	83	82	82	80	80																
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	88	86	85	85	83	82	80	80	78	78	76	76	72																
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	88	86	85	85	83	82	80	80	78	78	76	76	74	74	72																
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	80	80	78	78	76	76	74	74	72	72	70	70	69																
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76	76	74	74	72	72	70	70	69	69	67	67	65																
6	92	84	79	75	91	84	79	75	82	78	75	81	77	74	80	76	74	72	72	70	70	69	69	67	67	65	65	63	63	62																
7	88	80	75	71	87	80	75	71	78	74	71	77	73	70	76	73	70	69	69	67	67	65	65	63	63	62	62	60	60	59																
8	85	76	71	68	84	76	71	67	75	70	67	74	70	67	73	69	67	65	65	63	63	62	62	60	60	59	59	57	57	55																
9	81	73	68	64	80	72	68	64	72	67	64	71	67	64	70	66	64	62	62	60	60	59	59	57	57	55	55	53	53	51																
10	78	70	65	61	77	69	64	61	69	64	61	68	64	61	67	63	61	59	59	57	57	55	55	53	53	51	51	49	49	47																

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1548317
5°	1516791
10°	1410489
15°	1231507
20°	1019598
25°	779857
30°	426751
35°	157979
40°	54679
45°	24629
50°	11590
55°	5763
60°	1677
65°	934
70°	1154
75°	0
80°	0
85°	0



TEST NUMBER: P280927

CATALOG NUMBER: LDA2B209040D010 EU2B20WFL559040 2LBALD1WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	284.6	15.7
10°-20°	666.4	36.8
20°-30°	629.9	34.7
30°-40°	193.9	10.7
40°-50°	30.6	1.7
50°-60°	6.5	0.4
60°-70°	0.9	0.0
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1580.9	87.2
0°-40°	1774.8	97.9
0°-60°	1811.9	99.9
0°-90°	1812.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1812.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3138	
5°	3063	285
15°	2411	666
25°	1433	630
35°	262	194
45°	35	31
55°	7	6
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P280927

CATALOG NUMBER: LDA2B209040D010 EU2B20WFL559040 2LBALD1WH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3138.3
1°	3126.6
2°	3112.3
3°	3100.5
4°	3085.4
5°	3062.7
6°	3033.3
7°	2993.7
8°	2940.8
9°	2879.4
10°	2815.5
11°	2744.9
12°	2670.1
13°	2588.5
14°	2503.6
15°	2411.1
17.5°	2166.5
20°	1942.0
22.5°	1714.2
25°	1432.6
27.5°	1092.9
30°	749.1
32.5°	459.9
35°	262.3
37.5°	146.3
40°	84.9
42.5°	53.0
45°	35.3
47.5°	23.5
50°	15.1
52.5°	10.1
55°	6.7
57.5°	4.2
60°	1.7
62.5°	0.8
65°	0.8
67.5°	0.8
70°	0.8
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P280927

CATALOG NUMBER: LDA2B209040D010 EU2B20WFL559040 2LBALD1WH

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)