

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P278930

Luminaire Tested: **LDA2B159727D010 EU2B15NFL259727 2LBAD1H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P278930
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-2)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B159727D010 EU2B15NFL259727 2LBAD1H
Description: PORTFOLIO 2in ADJ 1500 LUMEN LED LUMINAIRE WITH NARROW FLOOD OPTIC
AND 2in ADJ spun Refl, Self-Flanged, H
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1049.0 lumens
Efficiency: N/A
Efficacy: 74.4 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.39
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P278930

CATALOG NUMBER: LDA2B159727D010 EU2B15NFL259727 2LBAD1H

Luminous Intensity Polar Plot





TEST NUMBER: P278930

CATALOG NUMBER: LDA2B159727D010 EU2B15NFL259727 2LBAD1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									20
RC	80									50									30									10									0									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100												100																
1	115	113	111	110	113	111	109	108	107	106	105	103	102	102	100	99	99	97												97																
2	112	108	105	103	110	107	104	102	103	101	100	101	99	98	98	97	96	94												94																
3	108	104	100	98	107	103	99	97	100	98	95	98	96	94	96	94	93	91												91																
4	105	100	96	94	104	99	96	93	97	94	92	95	93	91	94	92	90	89												89																
5	102	97	93	90	101	96	92	90	94	91	89	93	90	88	92	89	87	86												86																
6	100	94	90	87	98	93	89	87	92	89	86	91	88	86	89	87	85	84												84																
7	97	91	87	84	96	90	87	84	89	86	84	88	85	83	87	85	83	82												82																
8	95	88	85	82	94	88	84	82	87	84	81	86	83	81	85	83	81	80												80																
9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78												78																
10	90	84	80	78	90	84	80	78	83	80	77	82	79	77	82	79	77	76												76																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2684826
5°	2476083
10°	1668540
15°	822690
20°	351399
25°	138160
30°	54405
35°	23850
40°	11464
45°	5512
50°	3070
55°	1720
60°	987
65°	584
70°	721
75°	0
80°	0
85°	0



TEST NUMBER: P278930

CATALOG NUMBER: LDA2B159727D010 EU2B15NFL259727 2LBAD1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	423.5	40.4
10°-20°	456.1	43.5
20°-30°	131.7	12.6
30°-40°	27.8	2.7
40°-50°	6.8	0.7
50°-60°	2.0	0.2
60°-70°	0.7	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1011.3	96.4
0°-40°	1039.1	99.1
0°-60°	1048.0	99.9
0°-90°	1049.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1049.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5442	
5°	5000	424
15°	1611	456
25°	254	132
35°	40	28
45°	8	7
55°	2	2
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P278930

CATALOG NUMBER: LDA2B159727D010 EU2B15NFL259727 2LBAD1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	5441.9
1°	5407.8
2°	5349.9
3°	5271.7
4°	5160.9
5°	4999.7
6°	4782.0
7°	4498.1
8°	4148.8
9°	3741.7
10°	3330.6
11°	2915.1
12°	2522.8
13°	2174.6
14°	1868.4
15°	1610.7
17.5°	1064.5
20°	669.3
22.5°	411.6
25°	253.8
27.5°	154.8
30°	95.5
32.5°	60.4
35°	39.6
37.5°	26.2
40°	17.8
42.5°	12.4
45°	7.9
47.5°	4.9
50°	4.0
52.5°	3.0
55°	2.0
57.5°	1.5
60°	1.0
62.5°	1.0
65°	0.5
67.5°	0.5
70°	0.5
72.5°	0.5
75°	0.0
77.5°	0.5
80°	0.0
82.5°	0.0



TEST NUMBER: P278930

CATALOG NUMBER: LDA2B159727D010 EU2B15NFL259727 2LBAD1H

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)