

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P280723

Luminaire Tested: **LDA2B159727D010 EU2B15WFL559727 2LBAD1LI**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P280723  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-5)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA2B159727D010 EU2B15WFL559727 2LBAD1LI  
Description: PORTFOLIO 2IN ADJ 1500 LUMEN LED LUMINAIRE WITH WIDE FLOOD OPTIC AND  
2in ADJ spun Refl, Self-Flanged, LI  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1073.3 lumens  
Efficiency: N/A  
Efficacy: 76.1 lumens/watt  
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.73  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P280723

CATALOG NUMBER: LDA2B159727D010 EU2B15WFL559727 2LBAD1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P280723

CATALOG NUMBER: LDA2B159727D010 EU2B15WFL559727 2LBAD1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	112	109	107	112	110	108	106	106	104	103	102	101	99	98	97	97	95																			
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	90																			
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	88	86	85																			
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	80																			
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76																			
6	92	84	79	75	91	84	79	75	82	78	75	81	77	74	80	76	74	72																			
7	88	80	75	71	87	80	75	71	78	74	71	77	73	70	76	73	70	69																			
8	85	76	71	68	84	76	71	67	75	70	67	74	70	67	73	69	67	65																			
9	81	73	68	64	80	72	68	64	72	67	64	71	67	64	70	66	64	62																			
10	78	70	65	61	77	69	64	61	69	64	61	68	64	61	67	63	61	59																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	916617
5°	897931
10°	835021
15°	729067
20°	603621
25°	461676
30°	252598
35°	93535
40°	32395
45°	14582
50°	6908
55°	3441
60°	987
65°	584
70°	721
75°	0
80°	0
85°	0



TEST NUMBER: P280723

CATALOG NUMBER: LDA2B159727D010 EU2B15WFL559727 2LBAD1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	168.5	15.7
10°-20°	394.5	36.8
20°-30°	372.9	34.7
30°-40°	114.8	10.7
40°-50°	18.1	1.7
50°-60°	3.9	0.4
60°-70°	0.6	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	935.9	87.2
0°-40°	1050.7	97.9
0°-60°	1072.7	99.9
0°-90°	1073.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1073.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1858	
5°	1813	168
15°	1427	395
25°	848	373
35°	155	115
45°	21	18
55°	4	4
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P280723

CATALOG NUMBER: LDA2B159727D010 EU2B15WFL559727 2LBAD1LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1857.9
1°	1850.9
2°	1842.5
3°	1835.5
4°	1826.5
5°	1813.1
6°	1795.7
7°	1772.3
8°	1740.9
9°	1704.6
10°	1666.8
11°	1625.0
12°	1580.7
13°	1532.4
14°	1482.1
15°	1427.4
17.5°	1282.6
20°	1149.7
22.5°	1014.8
25°	848.1
27.5°	647.0
30°	443.4
32.5°	272.2
35°	155.3
37.5°	86.6
40°	50.3
42.5°	31.4
45°	20.9
47.5°	13.9
50°	9.0
52.5°	6.0
55°	4.0
57.5°	2.5
60°	1.0
62.5°	0.5
65°	0.5
67.5°	0.5
70°	0.5
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P280723

CATALOG NUMBER: LDA2B159727D010 EU2B15WFL559727 2LBAD1LI

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)