

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P499657

Luminaire Tested: **LDA2B159727R35D010 2LBDC1MMS**

Issue Date: 3/12/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P499657  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-27)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/12/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B159727R35D010 2LBDC1MMS  
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 97 CRI LEDS AND 2700K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 997.7 lumens  
Efficiency: N/A  
Efficacy: 70.8 lumens/watt  
Spacing Criteria (0/90/45): 0.55 / 0.55 / 0.5  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 14.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P499657

CATALOG NUMBER: LDA2B159727R35D010 2LBDC1MMS

### Luminous Intensity Polar Plot





TEST NUMBER: P499657

CATALOG NUMBER: LDA2B159727R35D010 2LBDC1MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	
1	115	113	111	109	112	111	109	107	107	105	104	103	102	101	100	99	98	96	96	96	96	
2	111	107	104	101	109	106	103	100	102	100	98	100	98	96	97	95	94	93	93	93	93	
3	107	102	99	96	105	101	98	95	99	96	93	96	94	92	94	92	91	89	89	89	89	
4	104	98	94	91	102	97	93	90	95	92	89	93	90	88	91	89	87	86	86	86	86	
5	100	94	90	87	99	93	89	86	92	88	86	90	87	85	89	86	84	83	83	83	83	
6	97	91	86	83	96	90	86	83	89	85	82	87	84	82	86	83	81	80	80	80	80	
7	94	87	83	80	93	87	83	80	86	82	79	85	81	79	84	81	79	78	78	78	78	
8	91	84	80	77	90	84	80	77	83	79	77	82	79	76	81	78	76	75	75	75	75	
9	89	82	77	75	88	81	77	74	80	77	74	80	76	74	79	76	74	73	73	73	73	
10	86	79	75	72	85	79	75	72	78	74	72	77	74	72	77	74	72	71	71	71	71	

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1567904
5°	1508273
10°	1365952
15°	950841
20°	465959
25°	173816
30°	76338
35°	37101
40°	17003
45°	9210
50°	4528
55°	1290
60°	493
65°	584
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P499657

CATALOG NUMBER: LDA2B159727R35D010 2LBDC1MMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	281.4	28.2
10°-20°	493.2	49.4
20°-30°	168.1	16.8
30°-40°	41.8	4.2
40°-50°	10.8	1.1
50°-60°	2.0	0.2
60°-70°	0.4	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	942.7	94.5
0°-40°	984.5	98.7
0°-60°	997.3	100.0
0°-90°	997.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	997.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3178	
5°	3046	281
15°	1862	493
25°	319	168
35°	62	42
45°	13	11
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P499657

CATALOG NUMBER: LDA2B159727R35D010 2LBDC1MMS

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3178.0
1°	3171.6
2°	3147.2
3°	3123.7
4°	3086.0
5°	3045.5
6°	3005.8
7°	2968.7
8°	2888.5
9°	2810.7
10°	2726.6
11°	2588.7
12°	2439.1
13°	2246.4
14°	2068.0
15°	1861.6
16°	1660.1
17°	1450.4
18°	1254.3
19°	1055.7
20°	887.5
21°	727.1
22.5°	533.5
23°	479.2
24°	391.2
25°	319.3
26°	264.1
27°	220.5
28°	185.8
29°	157.0
30°	134.0
32.5°	91.0
35°	61.6
37.5°	41.6
40°	26.4
42.5°	18.1
45°	13.2
47.5°	9.3
50°	5.9
52.5°	3.4
55°	1.5
57.5°	1.0
60°	0.5
62.5°	0.5
65°	0.5



TEST NUMBER: P499657

CATALOG NUMBER: LDA2B159727R35D010 2LBDC1MMS

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.5
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)