

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P280034

Luminaire Tested: **LDA2B209050D010 EU2B20FL409050 2LBAD1H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P280034
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-3)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B209050D010 EU2B20FL409050 2LBAD1H
Description: PORTFOLIO 2IN ADJ 2000 LUMEN LED LUMINAIRE WITH FLOOD OPTIC AND 2in
ADJ spun Refl, Self-Flanged, H
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1893.5 lumens
Efficiency: N/A
Efficacy: 91.9 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.55
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P280034

CATALOG NUMBER: LDA2B209050D010 EU2B20FL409050 2LBAD1H

Luminous Intensity Polar Plot





TEST NUMBER: P280034

CATALOG NUMBER: LDA2B209050D010 EU2B20FL409050 2LBAD1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100													100															
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96													96															
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92													92															
3	107	102	98	95	105	101	97	94	98	95	93	96	94	92	94	92	90	89													89															
4	103	98	93	90	102	97	93	90	95	91	89	93	90	88	91	89	87	85													85															
5	100	94	89	86	98	93	89	86	91	88	85	90	87	84	88	86	83	82													82															
6	97	90	85	82	95	89	85	82	88	84	82	87	83	81	85	83	80	79													79															
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77													77															
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74													74															
9	88	81	76	73	87	80	76	73	79	76	73	79	75	73	78	75	73	72													72															
10	85	78	74	71	84	78	74	71	77	73	71	76	73	70	76	72	70	69													69															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2603569
5°	2548538
10°	2322810
15°	1814546
20°	1074305
25°	399346
30°	124818
35°	55470
40°	25762
45°	12140
50°	6678
55°	3699
60°	1677
65°	1051
70°	1298
75°	0
80°	0
85°	0



TEST NUMBER: P280034

CATALOG NUMBER: LDA2B209050D010 EU2B20FL409050 2LBAD1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	475.7	25.1
10°-20°	945.9	50.0
20°-30°	387.4	20.5
30°-40°	64.1	3.4
40°-50°	15.2	0.8
50°-60°	4.0	0.2
60°-70°	1.0	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1809.0	95.5
0°-40°	1873.2	98.9
0°-60°	1892.4	99.9
0°-90°	1893.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1893.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5277	
5°	5146	476
15°	3553	946
25°	734	387
35°	92	64
45°	17	15
55°	4	4
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P280034

CATALOG NUMBER: LDA2B209050D010 EU2B20FL409050 2LBAD1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	5277.2
1°	5259.0
2°	5234.6
3°	5212.9
4°	5184.2
5°	5146.0
6°	5089.5
7°	5015.6
8°	4910.4
9°	4782.6
10°	4636.6
11°	4467.1
12°	4275.8
13°	4057.7
14°	3815.1
15°	3552.6
17.5°	2817.2
20°	2046.2
22.5°	1310.0
25°	733.6
27.5°	386.8
30°	219.1
32.5°	139.1
35°	92.1
37.5°	60.8
40°	40.0
42.5°	26.1
45°	17.4
47.5°	12.2
50°	8.7
52.5°	6.1
55°	4.3
57.5°	2.6
60°	1.7
62.5°	0.9
65°	0.9
67.5°	0.9
70°	0.9
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P280034

CATALOG NUMBER: LDA2B209050D010 EU2B20FL409050 2LBAD1H

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)