

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P499730

Luminaire Tested: **LDA2B159727R65D010 2LBD1WH**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P499730  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-66)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/8/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B159727R65D010 2LBD1WH  
Description: 1500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 97 CRI LEDS AND 2700K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 990.2 lumens  
Efficiency: N/A  
Efficacy: 70.2 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.95  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 14.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P499730

CATALOG NUMBER: LDA2B159727R65D010 2LBD1WH

### Luminous Intensity Polar Plot





TEST NUMBER: P499730

CATALOG NUMBER: LDA2B159727R65D010 2LBD1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75
5	92	83	78	73	90	82	77	73	81	76	72	79	75	72	77	74	71	69
6	87	78	72	68	86	77	72	67	76	71	67	74	70	66	73	69	66	65
7	83	73	67	63	81	73	67	63	71	66	62	70	65	62	69	65	62	60
8	78	69	63	58	77	68	62	58	67	62	58	66	61	58	65	61	58	56
9	75	65	59	55	73	64	58	54	63	58	54	62	58	54	61	57	54	53
10	71	61	55	51	70	61	55	51	60	55	51	59	54	51	58	54	51	49

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	538011
5°	494751
10°	472818
15°	454071
20°	418235
25°	387315
30°	354914
35°	260668
40°	123462
45°	40607
50°	13125
55°	1720
60°	987
65°	584
70°	721
75°	0
80°	0
85°	0



TEST NUMBER: P499730

CATALOG NUMBER: LDA2B159727R65D010 2LBD1WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	93.9	9.5
10°-20°	247.2	25.0
20°-30°	328.0	33.1
30°-40°	259.5	26.2
40°-50°	56.7	5.7
50°-60°	4.2	0.4
60°-70°	0.6	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	669.0	67.6
0°-40°	928.5	93.8
0°-60°	989.4	99.9
0°-90°	990.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	990.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1090	
5°	999	94
15°	889	247
25°	712	328
35°	433	259
45°	58	57
55°	2	4
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P499730

CATALOG NUMBER: LDA2B159727R65D010 2LBD1WH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1090.5
1°	1084.6
2°	1064.5
3°	1042.5
4°	1019.5
5°	999.0
6°	985.8
7°	972.6
8°	963.8
9°	950.6
10°	943.8
11°	933.0
12°	920.8
13°	910.0
14°	897.8
15°	889.0
16°	866.5
17°	855.2
18°	836.7
19°	819.6
20°	796.6
21°	778.0
22.5°	753.5
23°	746.7
24°	728.1
25°	711.5
26°	701.2
27°	684.1
28°	667.5
29°	647.4
30°	623.0
32.5°	537.9
35°	432.8
37.5°	308.6
40°	191.7
42.5°	108.1
45°	58.2
47.5°	31.3
50°	17.1
52.5°	7.3
55°	2.0
57.5°	1.0
60°	1.0
62.5°	0.5
65°	0.5



TEST NUMBER: P499730

CATALOG NUMBER: LDA2B159727R65D010 2LBD1WH

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.5
70°	0.5
72.5°	0.5
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)