

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P279139

Luminaire Tested: **LDA2B209050D010 EU2B20NFL259050 2LBAD1LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P279139
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-2)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B209050D010 EU2B20NFL259050 2LBAD1LI
Description: PORTFOLIO 2IN ADJ 2000 LUMEN LED LUMINAIRE WITH NARROW FLOOD OPTIC AND 2in ADJ spun Refl, Self-Flanged, LI
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1843.1 lumens
Efficiency: N/A
Efficacy: 89.5 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.39
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P279139

CATALOG NUMBER: LDA2B209050D010 EU2B20NFL259050 2LBAD1LI

Luminous Intensity Polar Plot





TEST NUMBER: P279139

CATALOG NUMBER: LDA2B209050D010 EU2B20NFL259050 2LBAD1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100	100													
1	115	113	111	110	113	111	109	108	107	106	105	103	102	102	100	99	99	97	97	97	97	97	97	97													
2	112	108	105	103	110	107	104	102	103	101	100	101	99	98	98	97	96	94	94	94	94	94	94	94													
3	108	104	100	98	107	103	99	97	100	98	95	98	96	94	96	94	93	91	91	91	91	91	91	91													
4	105	100	96	94	104	99	96	93	97	94	92	95	93	91	94	92	90	89	89	89	89	89	89	89													
5	102	97	93	90	101	96	92	90	94	91	89	93	90	88	92	89	87	86	86	86	86	86	86	86													
6	100	94	90	87	98	93	89	87	92	89	86	91	88	86	89	87	85	84	84	84	84	84	84	84													
7	97	91	87	84	96	90	87	84	89	86	84	88	85	83	87	85	83	82	82	82	82	82	82	82													
8	95	88	85	82	94	88	84	82	87	84	81	86	83	81	85	83	81	80	80	80	80	80	80	80													
9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78	78	78	78	78	78	78													
10	90	84	80	78	90	84	80	78	83	80	77	82	79	77	82	79	77	76	76	76	76	76	76	76													

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4717476
5°	4350640
10°	2931792
15°	1445518
20°	617429
25°	242732
30°	95593
35°	41859
40°	20158
45°	9698
50°	5373
55°	3011
60°	1677
65°	1051
70°	1298
75°	0
80°	0
85°	0



TEST NUMBER: P279139

CATALOG NUMBER: LDA2B209050D010 EU2B20NFL259050 2LBAD1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	744.1	40.4
10°-20°	801.4	43.5
20°-30°	231.4	12.6
30°-40°	48.8	2.7
40°-50°	12.0	0.7
50°-60°	3.5	0.2
60°-70°	1.2	0.1
70°-80°	0.6	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1777.0	96.4
0°-40°	1825.8	99.1
0°-60°	1841.3	99.9
0°-90°	1843.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1843.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9562	
5°	8785	744
15°	2830	801
25°	446	231
35°	70	49
45°	14	12
55°	4	3
65°	1	1
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P279139

CATALOG NUMBER: LDA2B209050D010 EU2B20NFL259050 2LBAD1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	9561.9
1°	9501.9
2°	9400.2
3°	9262.9
4°	9068.2
5°	8784.8
6°	8402.4
7°	7903.5
8°	7289.8
9°	6574.5
10°	5852.2
11°	5122.1
12°	4432.8
13°	3820.9
14°	3282.9
15°	2830.1
17.5°	1870.5
20°	1176.0
22.5°	723.2
25°	445.9
27.5°	272.1
30°	167.8
32.5°	106.0
35°	69.5
37.5°	46.1
40°	31.3
42.5°	21.7
45°	13.9
47.5°	8.7
50°	7.0
52.5°	5.2
55°	3.5
57.5°	2.6
60°	1.7
62.5°	1.7
65°	0.9
67.5°	0.9
70°	0.9
72.5°	0.9
75°	0.0
77.5°	0.9
80°	0.0
82.5°	0.0



TEST NUMBER: P279139

CATALOG NUMBER: LDA2B209050D010 EU2B20NFL259050 2LBAD1LI

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)